


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/19/10	D.GRIFFIN



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMRRSJAXXX	WHERE XXX = LENGTH IN FEET	CA-NMRRSJA010 (10 FEET)
CA-NMRRSJANXX	WHERE NXX = LENGTH IN INCHES	CA-NMRRSJAN16 (16 INCHES)
CA-NMRRSJAMXX	WHERE MXX = LENGTH IN METERS	CA-NMRRSJAM07 (7 METERS)
CA-NMRRSJAXMX	WHERE XMX = LENGTH IN DECIMAL METERS	CA-NMRRSJA3M5 (3.5 METERS)

RoHS Compliant ✓

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.PARHAM APPROVED BY K.BURGNER	DATE 3/18/10 3/18/10 3/18/10		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY COAXIAL	PRODUCT DESCRIPTION CA, CA195 NM RA/RP-SMA JACK
FSCM NO. 43321		DWG. NO. CA-NMRRSJA	REV. A	SCALE: NONE CAD FILE: CA-NMRRSJA.SLDDRW SHEET 1 OF 1