


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/24/10	D.GRIFFIN



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMRSMA $\underline{\text{XXX}}$	WHERE XXX = LENGTH IN FEET	CA-QPNMA010 (10 FEET)
CA-NMRSMA $\underline{\text{NXX}}$	WHERE NXX = LENGTH IN INCHES	CA-QPNMA16 (16 INCHES)
CA-NMRSMA $\underline{\text{MXX}}$	WHERE MXX = LENGTH IN METERS	CA-QPNMAM07 (7 METERS)
CA-NMRSMA $\underline{\text{XMX}}$	WHERE XMX = LENGTH IN DECIMAL METERS	CA-QPNMA3M5 (3.5 METERS)

NOTE:

1. CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLIES TO BE PACKAGED INDIVIDUALLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$.XX = $\pm .02$.XXX = $\pm .005$	APPROVALS DRAWN BY D. CASTRO CHECKED BY C. BRAN APPROVED BY K. BURGNER	DATE 3/19/10 3/19/10 3/19/10	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY COAXIAL
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. CA-NMRSMA		SCALE: NONE	CAD FILE: CA-NMRSMA.SLDDRW
SHEET 1 OF 1		REV. A		