

WIRE MAP							
"P1"	"P2"	COLOR					
CENTER CONTACT	CENTER CONTACT	HIGH (+) BLUE WIRE					
CYLINDRICAL CONTACT	CYLINDRICAL CONTACT	LOW (-) WHITE WIRE					
CONNECTOR BODY	CONNECTOR BODY	CABLE SHIELD					

LENGTH CODE CHART							
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED					
CA-TRBP-PRXXX	WHERE XXX = LENGTH IN FEET	CA-TRBP-PR010 (10 FEET)					
CA-TRBP-PRNXX	WHERE NXX = LENGTH IN INCHES	CA-TRBP-PR16 (16 INCHES)					
CA-TRBP-PR <u>MXX</u>	WHERE MXX = LENGTH IN METERS	CA-TRBP-PRM07 (7 METERS)					
CA-TRBP-PRXMX	WHERE XMX = LENGTH IN DECIMAL METERS	CA-TRBP-PR3M5 (3.5 METERS)					

		UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS DRAWN BY D. CASTRO	DATE 6/30/10			NORTH AND	NOOD DRIVE NDOVER, MA 1845				
DTES:				≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [2049] ≤200 [37(20] = +4 [152] / -0	CHECKED BY K. BURGNER APPROVED BY K. BURGNER	6/30/10 6/30/10	CATEGORY					A
CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH LCOM SPEC. PS-0031			>300 [/620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .02 .XXX = ±.005	CONFIGURATIO UNDIMENSIONI MAY V	CA,M17/176-00002 TRB P/PR					-		
				COLOR VARIATIONS MAY OCCUR		SIZE A	43321	DWG. NO. CA-1		REV. A SHEET 1 OF 1		
8	7	6	5	<b>↑</b> 4	3			2		1		

В

NOTES:

В

А

1. CABLE ASSEMBLY SHA 2. CABLE ASSEMBLY SHA