



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/2/12	D.GRIFFIN
B	ECN 6451: UPDATED NOTES & WIRING MAP. CHANGED EXPOSED CONN. DIM.	10/10/12	D. DESJARDIN



MODEL NUMBER	LENGTH	
	METERS	[FEET]
CAA-90DMICB-03M	.3	[.98]
CAA-90DMICB-05M	.5	[1.64]
CAA-90DMICB-075M	.75	[2.46]
CAA-90DMICB-1M	1.0	[3.28]
CAA-90DMICB-2M	2.0	[6.56]
CAA-90DMICB-3M	3.0	[9.84]
CAA-90DMICB-5M	5.0	[16.41]



NOTES:

1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. FRISIELLO	5/20/11		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY D. CASTRO	5/20/11	PRODUCT DESCRIPTION	
PROJECTION 	APPROVED BY S. SMITH	5/20/11	CA USB STR A-M/90DN MICB	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO. CAA-90DMICB	REV. B
			SCALE: NONE	CAD FILE: CAA-90DMICB.SLDDRW
				SHEET 1 OF 1