



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/2/13	D.GRIFFIN



MODEL NO.	LENGTH METERS [FEET]
CSMUAA-PL-03M	0.3 [.98]
CSMUAA-PL-05M	0.5 [1.64]
CSMUAA-PL-1M	1.0 [3.28]
CSMUAA-PL-2M	2.0 [6.56]
CSMUAA-PL-3M	3.0 [9.84]
CSMUAA-PL-4M	4.0 [13.12]
CSMUAA-PL-5M	5.0 [16.41]

NOTES:

CABLE:
 UL STYLE 2725,
 ONE 28AWG STRANDED TINNED COPPER TWISTED PAIR
 TWO 20AWG STRANDED TINNED COPPER CONDUCTORS
 OVERALL ALUMINIZED POLYESTER SHIELD WITH DRAIN WIRE.
 PVC OUTER JACKET, BLACK

MISCELLANEOUS:

1. PLASTIC CRUSH RESISTANCE: 800 PSI (MIN.)
2. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
3. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 ROHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	1/3/12		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. FRISIELLO	1/11/13	PRODUCT DESCRIPTION CA USB 2.0 A/A PLAS ARMR	
PROJECTION 	APPROVED BY S. SMITH	1/24/13	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321
			DWG. NO. CSMUAA-PL	REV. A
			CAD FILE: CSMUAA-PL.SLDDRW	SHEET 1 OF 1