


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN INITIAL RELEASE	07/24/2014	B. ZHANG



2x, 20 PIN DISPLAYPORT MALE
30µ" SELECTIVE GOLD PLATED CONTACTS
NICKEL PLATED SHELL

2X PLASTIC HOOD,
BLACK

UL20276, DISPLAYPORT CABLE
(5) SHIELDED TWISTED PAIR 30AWG
WITH 30 AWG DRAIN WIRE.
(4) 30 AWG SINGLE CONDUCTORS.
PVC JACKET: BLACK.

WIRING MAP

CABLE	"P1"	SIGNAL NAME	COLOR	"P2"
TWISTED PAIR 1	1	ML_LANE 0(p)	BROWN	12
	2	GND	DRAIN	11
	3	ML_LANE 0(n)	WHITE	10
TWISTED PAIR 2	4	ML_LANE 1(p)	RED	9
	5	GND	DRAIN	8
	6	ML_LANE 1(n)	WHITE	7
TWISTED PAIR 3	7	ML_LANE 2(p)	GREEN	6
	8	GND	DRAIN	5
	9	ML_LANE 2(n)	WHITE	4
TWISTED PAIR 4	10	ML_LANE 3(p)	ORANGE	3
	11	GND	DRAIN	2
	12	ML_LANE 3(n)	WHITE	1
	13	GND	BROWN	13
	14	GND	RED	14
TWISTED PAIR 5	15	AUX CH(p)	BLUE	15
	16	GND	DRAIN	16
	17	AUX CH(n)	WHITE	17
	18	HOT PLUG DETECT	YELLOW	18
	19	DP_PWR RETURN	ORANGE	19
	20	N/A	N/C	20
SHELL		GND	BRAID	SHELL

PART NUMBER	LENGTH	
	METERS	FEET
DPCAMMSB-0.5	0.5	1.64
DPCAMMSB-1	1.0	3.28
DPCAMMSB-2	2.0	6.56
DPCAMMSB-3	3.0	9.84
DPCAMMSB-5	5.0	16.41
DPCAMMSB-10	10.0	32.81
DPCAMMSB-15	15.0	49.22

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY B. ZHANG CHECKED BY F. MAO APPROVED BY T. LU	DATE 10/16/2013 10/16/2013 10/16/2013	L-com Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY AUDIO/VIDEO	PRODUCT DESCRIPTION DP CABLE, SHORT BODY M/M	SCALE: NONE CAD FILE: DPCAMMSB-X.SLDDRW
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. DPCAMMSB-X
		SHEET 1 OF 1	REV. A	