


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/23/13	D.GRIFFIN
B	ECN 6873: UL21100 WAS UL20276, REVISED ROHS NOTE	6/3/13	D.FRISIELLO
C	ECN8182: UPT DWG FROM MOLDED THUMBSCREW TO METAL THUMBSCREW	11/30/2015	B.ZHANG




UL STYLE 21100,  
 (7) SHIELDED TWISTED PAIR, 28AWG, STRANDED TINNED COPPER,  
 (1) UNSHIELDED TWISTED PAIR, 28AWG, STRANDED TINNED COPPER,  
 (3) CONDUCTORS, 28AWG, STRANDED TINNED COPPER,  
 SHIELDING(BRAIDED): 36AWG TINNED COPPER  
 SHIELDING: ALUMINUM/POLYESTER  
 OUTER JACKET: LOW SMOKE ZERO HALOGEN, BLACK

MODEL NUMBER	LENGTH	
	FEET	METERS
DVIDD-RA4Z-1	1.0	.31
DVIDD-RA4Z-3	3.0	.91
DVIDD-RA4Z-5	5.0	1.52
DVIDD-RA4Z-10	10.0	3.05
DVIDD-RA4Z-15	15.0	4.57

**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: $X = \pm .2$ [5.08] $.XX = \pm .02$ [.51] $.XXX = \pm .005$ [.13]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY R.SCOTT APPROVED BY S.SMITH	DATE 4/17/13 4/17/13 4/17/13	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY <b>AUDIO/VIDEO</b>	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
		DWG. NO. <b>DVIDD-RA4Z</b>	REV. <b>C</b>
		SCALE: NONE	CAD FILE: DVIDD-RA4Z.SLDDRW
		SHEET 1 OF 1	