
REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
Α	REV A DRAWING RELEASED	03/25/2019	PHOSPODAR



PART NUMBER	LENGTH METERS [FEET]
FODLC-OM5-1	1.0 [3.28]
FODLC-OM5-3	3.0 [9.84]
FODLC-OM5-5	5.0 [16.41]
FODLC-OM5-7	7.0 [22.97]
FODLC-OM5-10	10.0 [32.81]
FODLC-OM5-15	15.0 [49.22]
FODLC-OM5-20	20.0 [65.62]
FODLC-OM5-25	25.0 [82.03]

UNLESS OTHERWISE SPECIFIED THE INFORMATION AND DESIGN IN THIS DOCUMENT LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY TOLERANCES: an INFINIT® brand ALL RIGHTS RESERVED. .X=± .2 [5.08] **FRACTIONS** 50 High Street, West Mill, 3rd Floor, Suite #30 .XX=± .01 [.25] ± 1/32 SHEET North Andover, MA 01845 USA. XXX=± .005 [.13] ANGLES ± 1° Phone: 1.800.341.5266 | 1.978.682.6936 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. Fax: 1.978.689.9484 SCALE N/A www.L-com.com | e-mail: CustomerService@L-com.com THIRD-ANGLE PROJECTION SIZE CAGE DRAWN BY PART NUMBER REV (\oplus) FODLC-OM5 Α 43321 **DFRISIELLO**

Α

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.