


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/08/04	MCCORMICK
B	ECN# 2248 CONSTRUCTION FROM 1.6mm TO 3.0mm	11/11/05	MCCORMICK



PART NUMBER	LENGTH METERS
FODPST50-01	1.0
FODPST50-02	2.0
FODPST50-03	3.0
FODPST50-04	4.0
FODPST50-05	5.0

NOTES:

1.0 TEST:

1.1 BACK REFLECTION TESTED AT 1310nm WITH A <-40.0 dB RESULT MIN.

2.0 PACKAGING:

2.1 THE PRODUCT SHALL BE PRESERVED & PACKAGED IN A MANNER WHICH WILL AFFORD ADEQUATE PROTECTION AGAINST CORROSION, DETERIORATION, AND PHYSICAL DAMAGE DURING SHIPMENT.

2.2 INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG DEPICTED ON [1AN01-001-OD1](#) . MARK EACH BAG PER [LSP-010-1](#)

3.0 WORKMANSHIP:


3.1 CABLE ASSEMBLIES SHALL BE MANUFACTURED IN SUCH A MANNER AS TO BE UNIFORM IN QUALITY AND SHALL BE FREE FROM DEFECTS THAT WILL ADVERSELY AFFECT LIFE, SERVICEABILITY, OR APPEARANCE.

4.0 VISUAL AND MECHANICAL:

4.1. CABLE ASSEMBLIES SHALL BE INSPECTED TO VERIFY COMPLIANCE TO THIS DRAWING.

5.0 MANUFACTURING:

5.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.



UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
X ±.1
XX ±.05
XXX ±.005
CABLE LENGTH TOLERANCE
<300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	11/08/2004
CHECKED BY D.PARHAM	11/08/2004
APPROVED BY R.CARRICK	11/08/2004

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION 50/125 DUPLEX PLENUM CABLE ASSY			
DRAWING TITLE OUTLINE DRAWING			
SIZE A	FSCM NO. 43321	DWG. NO. FODPST50-01-OD1	REV. B
SCALE: NONE		CAD FILE: FODPST50-01-OD1.SLDDRW	SHEET 1 OF 1