


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/16/13	D.GRIFFIN



NOTES:

- 1- CRIMP SIZES: HEX DIE .068", .213", .256", .324"
 - 2- CABLE TYPE: LMR@@/WBC195, 200, 240, 300, HyperLink CA-195, 200, 240, 400, RG58, RG59, RG62, RG141, RG142, RG6, Belden 8240, 8219
 - 3- COMPONENT SHALL BE PACKAGED AS PER L-COM SPEC PKG-00012
- ALL DIMENSIONS FOR REFERENCE ONLY -

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY B.PUCHASKI	01/16/13			
DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005	CHECKED BY K.BURGNER	01/16/13	CATEGORY COAXIAL		
	APPROVED BY P.PESA	01/16/13			
ANGULAR TOLERANCES: ALL = ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION RATCHET CRIMPING TOOL W/ .068", .213", .256", AND .324" HEX DIE		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. HT-CRIMP04	REV. A
SCALE: NONE		CAD FILE: HT-CRIMP04.SLDDRW		SHEET 1 OF 1	