THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

 REVISIONS
 DATE
 APPROVAL

 A INITIAL RELEASE
 12/21/12
 D.FRISIELLO

RoHS Compliant ✓



· w/o lock and cut functions.

HT-	Crimping size					
310A	AWG	19-26(UR) 22-26(UY) 19-26(UG)				

NOTES:

ITEM SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

	APPROVALS	DATE	_					45 DEEOU!!	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	D.FRISIELLO	12/21/12	Global 45 BEECHWOOD Connectivity NORTH ANDOVE						NDOVER, MA
OVERALL CABLE LENGTH TOLERANCE: \$12 [305] = +1 [25] / - 0 \$12 [305] - 60 [1524] = +2 [51] / - 0 \$60 [1524] - 120 [3048] = +4 [102] / - 0 \$120 [3048] - 3007 (\$20] = +6 [152] / - 0	CHECKED BY D.FRISIELLO	12/21/12	CATEGO	DV	01845				
	APPROVED BY D.GALLAGHER	12/21/12	TELECOM/MODULAR						
>300/7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 .XX = .02 .XX = .005	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PARALLEL ACTION PLIERS						
PROJECTION (+)	COLOR VARIATIONS MAY OCCUR		SIZE		и NO. 321	DWG. NO.	HT100	8	A REV.
			SCALE: 1:1 CAD			D FILE: HT1008.SLDDRW			SHEET 1 OF 1