
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ~

	REVISIONS							
REV	DESCRIPTION	DATE	APPROVAL					
А	INITIAL RELEASE	10/3/12	D.FRISIELLO					



Specification : .

* Item No : HT-106He

Aø	B₄⊅	Crimping⊬ RG Cable Size⊬	
()±0.1	↓ ±0.1		
.359"(9.12mm)	.322 [~] (8.20mm)	F-59,62,6	

- * Length : 9" (229mm)
- * Weight : 680g

* Material :

Frame Is All Steel Constructions , With Black Oxide Finished.

Crimper Is Made Of Powder Alloy Steel And Harden.

* W/Adjustment

NOTES:

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1.

UNLESS OTHERWISE SPECIFIED.	APPROVALS	DATE				Global 45 BEECH	WOOD DRIVE
DIMENSIONS ARE IN INCHES [mm]	DRAWN BY D.FRISIELLO	10/3/12		C	j	Connectivity NORTH AN	DOVER, MA
OVERALL CABLE LENGTH TOLERANCE:	CHECKED BY D.DES.JARDIN	10/3/12					1845
≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0	APPROVED BY						
>60 [1524] - 120 [3048] = +4 [102] / -0 >120[3048] - 300[7620] = +6 [152] / -0	D.FRISIELLO	10/3/12	COAXIAL				
>300[7620] = +5% / -0%	CONFIGURATION DETAILS OF		PRODUCT DESCRIPTION				
XE OTHER DIMENSIONAL TOLERANCES. ,X = .2 ,XX = .02 ,XXX = .005	UNDIMENSIONED FEATURES MAY VARY		9"HEX CRIMP TOOL/ADJ RG59,62,6				
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCN 433		dwg. no. HT106H	REV.
\mathbf{Y}			SCALE: 1:1 CAD FILE: HT106H.SLDDRW		FILE: HT106H.SLDDRW	SHEET 1 OF 1	