	8 7 NFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE OUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.	6		5	+	4	REV A INI	3 TIAL RELEASE	DES	2 REVISION	IS	DATE 8/1/12	APPROVED D.GRIFFIN	
D														
С				FOR COND GREC USE TA IWAN										
•			Annalism has been able to be an an annalism an 											
В														
	NOTES: 1. CRIMP TOOL FOR RJ11/RJ12 PLUGS				DIMENSION	HERWISE SPECIFIED, S ARE IN INCHES [mm] LE LENGTH TOLERANCE:	APPROVALS DRAWN BY D. DESJARDIN	DATE 8/1/12	Ŀ		' Global Connectivity	NO DELLA NUE	OOD DRIVE DOVER, MA 845	
A	2. TOOL HAS CUT AND STRIP FUNCTIONS				<pre>>60 [1524] ≤1 >60 [1524] ≤1 >120 [3048] ≤1 >300 [1</pre>	Le LENGTH TOLERANCE: D5] = +1 [25] / -0 00 [1524] = +2 [51] / -0 20 [3048] = +4 [102] / -0 300 [7620] = +6 [152] / -0 '620] = +5% / -0%	CHECKED BY D. FRISIELLO APPROVED BY D. PARHAM	8/1/12	CATEGOR	TELECC	M/MODU			
	3. BLACK OXIDE FINISH 4. TOOL IS INDIVIDUALLY PACKAGED				ALL OTHER DIN	ALL OTHER DIMENSIONAL TOLERANCES: $X = \pm .2$ $XX = \pm .02$ $XXX = \pm .005$		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY						
								COLOR VARIATIONS MAY OCCUR		FSCM NO. DW 43321	G. NO. HT:	2096	A REV.	