
	REVISIONS						
	REV	DESCRIPTION	DATE	APPROVAL			
	Α	INITIAL RELEASE	9/28/12	D.FRISIELLO			
Γ							



NOTES:

COMPONENT SHALL BE PACKAGED PER L-COM SPECIFICATION LSP-010-1.

UNLESS OTHERWISE SPECIFIED,	APPROVALS DRAWN BY	DATE		$\overline{}$		Global 45 BEE	CHWOOD DRIVE
DIMENSIONS ARE IN INCHES [mm]	D.DESJARDIN 9/28/12		Connectivity NORTH ANDOVER, MA				
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / - 0	D.FRISIELLO	9/28/12	CATECO	CATEGORY			01045
>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120[3048] - 300[7620] = +6 [152] / -0	APPROVED BY D.FRISIELLO	9/28/12	TOOLS				
>300/7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES:	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION HEX CRIMP TOOL MULTI USE				
PROJECTION (+)	COLOR VARIATIONS MAY OCCUR		SIZE		м NO. 321	DWG. NO. HT301G	A REV.
9 -			SCALE:	1:1	CAD F	FILE: HT301G .SLDDRW	SHEET 1 OF 1