

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/28/13	D.GRIFFIN



NOTES:

1. FOR OUTER JACKETS AND INSULATION FROM 0.18" TO 1.12" [4.5 TO 28.5 mm] OD.
2. ADJUSTABLE CUTTING DEPTH UP TO 0.12" [3.0 mm].
3. APPROXIMATE DIMENSIONS: 5.3 X 1.6 X 0.6" [135 X 40 X 15 mm]
4. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005	APPROVALS DRAWN BY D. DESJARDIN	DATE 1/25/13	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY D. FRISIELLO APPROVED BY S. SMITH	DATE 1/25/13 1/28/13	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION STRIP TOOL, CABLE HEAVY DUTY	SCALE: NONE CAD FILE: MK02.SLDRW SHEET 1 OF 1
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. MK02
REV. A	REVISIONS		