
	REVISIONS				
R	REV	DESCRIPTION	DATE	APPROVED	
	В	ECN 9809: REVISED WIRE MAP TO 24 FIBER, TYPE B	04/25/2019	PHOSPODAR	



J1	COLOR	J2
1	BLUE	12
2	ORANGE	11
3	3 GREEN	
4	4 BROWN	
5	GRAY	8
6	WHITE	7
7	RED	6
8	BLACK	5
9	YELLOW	4
10	PURPLE	3
11	ROSE	2
12	AQUA	1
13	BLUE/BLACK	24
14	ORANGE/BLACK	23
15	GREEN/BLACK	22
16	BROWN/BLACK	21
17	GRAY/BLACK	20
18	WHITE/BLACK	19
19	RED/BLACK	18
20	BLACK / WHITE	17
21	YELLOW/BLACK	16
22	PURPLE/BLACK	15
23	ROSE/BLACK	14
24	AQUA/BLACK	13



PART NUMBER	METERS [FEET]
MPFF24OM5BR-1	1.0 [3.28]
MPFF24OM5BR-3	3.0 [9.84]
MPFF24OM5BR-5	5.0 [16.40]
MPFF24OM5BR-10	10.0 [32.81]
MPFF24OM5BR-25	25.0 [82.02]
MPFF24OM5BR-50	50.0 [164.04]
MPFF24OM5BR-100	100.0 [328.08]

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X=± .2 [5.08] FRACTIONS
.XX=± .01 [.25] ± 1/32
.XXX=± .005 [.13] ANGLES ± 1°

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. THIRD-ANGLE PROJECTION

⊕ ₇

an INFINIT® brand
High Street West Mill 3rd Floor

50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA. Phone: 1.800.341.5266 | 1.978.682.6936

Fax: 1.978.689.9484 www.L-com.com | e-mail: CustomerService@L-com.com

SCALE SCALE

SHEET

SCALE N/A

THE INFORMATION AND

DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
L-COM GLOBAL CONNECTIVITY

ALL RIGHTS RESERVED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

A 43321 DRAWN BY

MPFF24OM5BR