

THE IN	8 NFORMATION CONTAINED IN THIS	DRAWING IS THE SOLE	6	5 🛊 4	3	2	
PROPE	NFORMATION CONTAINED IN THIS ERTY OF L-COM, INC. ANY REPROD DUT THE WRITTEN PERMISSION OF L-C	UCTION IN PART OR WHOLE COM, INC. IS PROHIBITED.					
				<u>/c\</u>			
		T	CABLE CHAR				
	MODEL NUMBER	LENGTH, MTR [FT]	CABLE MODE	JACKET TYPE	CABLE COLOR		
	MPMM12OM1-1	1.0 [3.28]					
	MPMM12OM1-3	3.0 [9.84]	62.5/125 MULTIMODE OM1		ORANGE		
	MPMM12OM1-5	5.0 [16.41]					
	MPMM12OM1-10	10.0 [32.81]		OM1 OFNR (RISER) RATED			
	MPMM12OM1-25	25.0 [82.03]					
	MPMM12OM1-50	50.0 [164.05]					
	MPMM12OM1-100	100.0 [328.10]					
	MPMM12OM2-1	1.0 [3.28]	50/125 MULTIMODE OM2				
	MPMM12OM2-3	3.0 [9.84]			ORANGE		
	MPMM12OM2-5	5.0 [16.41]					
	MPMM12OM2-10	10.0 [32.81]		M2 OFNR (RISER) RATED			
	MPMM12OM2-25	25.0 [82.03]		,			
	MPMM12OM2-50	50.0 [164.05]					
	MPMM12OM2-100	100.0 [328.10]					
	MPMM12OM3-1	1.0 [3.28]	50/125 MULTIMODE OM3 LASER OPTIMIZED		AQUA		
	MPMM12OM3-3	3.0 [9.84]					
	MPMM12OM3-5	5.0 [16.41]					
	MPMM12OM3-10	10.0 [32.81]		M3 OFNR (RISER) RATED			
	MPMM12OM3-25	25.0 [82.03]					
	MPMM12OM3-50	50.0 [164.05]					
	MPMM12OM3-100	100.0 [328.10]					
	MPMM12OM4-1	1.0 [3.28]	- 50/125 MULTIMODE OM4 LASER OPTIMIZED		AQUA		
	MPMM12OM4-3	3.0 [9.84]					
	MPMM12OM4-5	5.0 [16.41]					
	MPMM12OM4-10	10.0 [32.81]		M4 LOW SMOKE ZERO HALOGEN			
	MPMM12OM4-25	25.0 [82.03]					
	MPMM12OM4-50	50.0 [164.05]					
	MPMM12OM4-100	100.0 [328.10]					
	MPMM12S-1	1.0 [3.28]	9/125 SINGLE MODE OS1				
	MPMM12S-3	3.0 [9.84]					
	MPMM12S-5	5.0 [16.41]				I - Carro Global	50 HIGH STREET NORTH ANDOVER, M
	MPMM12S-10	10.0 [32.81]		OS1 OFNR (RISER) RATED	YELLOW	Conne	ectivity 01845
	MPMM12S-25	25.0 [82.03]				CATEGORY	
	MPMM12S-50	50.0 [164.05]					OPTICS
	MPMM12S-100	100.0 [328.10]				PRODUCT DESCRIPTION	
							PO- M/M
						SIZE FSCM NO. DWG. NO. 43321	MPMM12
						SCALE: NONE CAD FILE: MPMM12	_
	8	7	6	5 4	3	2	1