THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS							
REV	DESCRIPTION	DATE	APPROVAL				
Α	INITIAL RELEASE	07/25/19	MMARTINEZ				

NB14-18-FRK-50F CONTAINS:

- 4 #6 U-TYPE SPEED NUT
- 4 #6 2.0 STAINLESS STEEL PAN HEAD PHILLIPS SHEET METAL SCREW
- 1 120x120mm ALUMINUM MESH FILTER
- 1 120x120x38mm 12VDC COOLING FAN 4.8W

		APPROVALS	DATE			_	0 5 1 1 5 2 1 1	
DIMENSIONS ARE IN INCHES [mm]		DRAWN BY DZINN	07/25/2019	_	C		Global 50 HIC Connectivity NORTH AI	SH STREET NDOVER. MA
		CHECKED BY					Connectivity	1845
`	≤12 [305] = +1 [25] / - 0	MMARTINEZ	07/25/2019	CATEGORY				
	>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0	APPROVED BY		ENCLOSURE				
>	×120[3048] - 300[7620] = +6 [152] / -0	MMARTINEZ	07/25/2019	LINCLOSORL				
	>300[7620] = +5% / -0%			PRODUCT DESCRIPTION				
ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [.51] .XXX = .005 [.13]		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		FAN REPL KIT-14/18" ENCL 12VDC				
PR	PROJECTION COLOR VARI			SIZE	FSCA 43		DWG. NO. NB14-18-FRK-50F	A REV.
	¥ —			SCALE:	NONE	CAD FIL	E: NB14-18-FRK-50F.SLDDRW	SHEET 1 OF 1