THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

	REVISIONS							
REV	DESCRIPTION	DATE	APPROVAL					
Α	INITIAL RELEASE	07/25/19	MMARTINEZ					

NB20-FHW-KIT CONTAINS:

- 4 #8 U-TYPE SPEED NUT
- 4 #8 2.5 STAINLESS STEEL PAN HEAD PHILLIPS SHEET METAL SCREW

	APPROVALS	DATE	_				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	DRAWN BY DZINN	07/25/2019	Ŀ			Coppectivity NORTH A	SH STREET NDOVER, MA
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / - 0	CHECKED BY MMARTINEZ	07/25/2019	CATEGO	1845			
>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120[3048] - 300[7620] = +6 [152] / -0	APPROVED BY MMARTINEZ	07/25/2019	ENCLOSURE				
>300[7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES:	CONFIGURATION DETAILS OF		PRODUCT DESCRIPTION				
.X = .2 [5.08] .XX = .02 [.51] .XXX = .005 [.13]	UNDIMENSIONED FEATURES MAY VARY		FAN HARDWARE KIT FOR NB20 ENCL				
PROJECTION (+)	COLOR VARIATIONS MAY OCCUR		SIZE	FSCA 433		DWG. NO. NB20-FHW-KIT	A REV.
Ψ			SCALE:	NONE	CAD F	FILE: NB20-FHW-KIT.SLDDRW	SHEET 1 OF 1