THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

	REVISIONS							
	REV	DESCRIPTION	DATE	APPROVAL				
	Α	INITIAL RELEASE	07/25/2019	MMARTINEZ				
ı								

## NB20-FRK-40F CONTAINS:

- 4 #8 U-TYPE SPEED NUT
- 4 #8 2.5 STAINLESS STEEL PAN HEAD PHILLIPS SHEET METAL SCREW
- 1 120X120mm ALUMINUM MESH FILTER
- 1 120x120x38mm 48VDC COOLING FAN 5.3W

	APPROVALS	DATE			_	<b>2 2 1 1 1 5 2 1 1</b>	
UNLESS OTHERWISE SPECIFIED,	DRAWN BY D7INN	07/25/2019		$\mathbf{C}$		Global 50 HIG Connectivity NORTH AN	SH STREET
DIMENSIONS ARE IN INCHES [mm]	CHECKED BY	0772072017				• • Connectivity	1845
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / - 0	MMARTINEZ	07/25/2019	CATEGO	CATEGORY			
>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0	APPROVED BY		CALLOC	ENCLOSURE			
>60 [1524] - 120 [3048] = +4 [102] / -0 >120[3048] - 300[7620] = +6 [152] / -0	MMARTINEZ	07/25/2019	LITOLOGOICE				
>300[7620] = +5% / -0%			PRODUCT DESCRIPTION				
ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [.51] .XXX = .005 [.13]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		FAN REPL KIT-20" ENCL 48VDC				
ROJECTION COLOR VARIATI MAY OCCU			SIZE FSCM NO. 43321			DWG. NO. NB20-FRK-40F	A REV.
Ť —			SCALE:	NONE	CAD	ILE: NB20-FRK-40F.SLDDRW	SHEET 1 OF 1