


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|----------|----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 05/10/17 | J.LABOY |
| | | | |
| | | | |



NOTES:

1. MATERIAL: .06 THICK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. SILKSCREEN COLOR: WHITE.
4. PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

REGULATORY COMPLIANCE:
CE 2011/65/EU(RoHS DIRECTIVE)

| | | | | |
|--|---|--|--|-----------------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] | APPROVALS DRAWN BY B.PUCHASKI CHECKED BY D.FRISIELLO APPROVED BY M.MARTINEZ | DATE 05/02/17 05/08/17 05/02/17 | 50 HIGH STREET NORTH ANDOVER, MA 01845 | |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | CATEGORY RACK/ENCLOSURE | |
| | COLOR VARIATIONS MAY OCCUR | | PRODUCT DESCRIPTION 2U PNL W/32 CAT6 SHIELDED MINI COUPLERS | |
| | PROJECTION | SIZE A | FSCM NO. 43321 | DWG. NO. PR35F504B-SC6M |

SCALE: NONE | CAD FILE: PR35F504B-SC6M.SLDDRW | SHEET 1 OF 1