


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL# RE07U-	
SUFFIX	CONNECTOR TYPE
NF	N-FEMALE
NM	N-MALE
RSP	RP SMA-PLUG
RMM	RP MMCX MALE
RTP	RP TNC-PLUG
RTJ	RP TNC-JACK
RNP	RP N-PLUG
RNJ	RP N-JACK
SM	SMA MALE
TM	TNC MALE
TF	TNC FEMALE
MC	MC CARD MALE
MM	MMCX MALE RIGHT ANGLE
MMS	MMCX MALE STRAIGHT
AM	ORINOCO COMPATIBLE TYPE

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/30/11	B.PUCHASKI
B	ECN5861: ADDED MMS. ADDED "RIGHT ANGLE" TO MM CONN TYPE	11/29/11	DFP
C	ECN 7405 UPDATE TO MATCH PHYSICAL PART	04/23/14	B.PUCHASKI
D	ECN 7699 UPDATE TO MATCH PHYSICAL PART	12/04/14	B.PUCHASKI



NOTES:
 PACKAGING:
 COMPONENT SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPEC PKG-00012

- ALL DIMENSIONS FOR REFERENCE-

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.PUCHASKI	08/30/11		
DIMENSIONAL TOLERANCES: .X = ±.1 [2.54] .XX = ±.01 [2.5] .XXX = ±.005 [1.3]	CHECKED BY P.PESA	08/30/11	CATEGORY ANTENNA	
	APPROVED BY P.PESA	08/30/11	PRODUCT DESCRIPTION 2.4GHz 7dBi OMNI ANTENNA W/4 FOOT CONNECTOR PIGTAIL	
ANGULAR TOLERANCES: ALL = ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
PROJECTION 	COLOR VARIATIONS MAY OCCUR		DWG. NO. RE07U	REV. D
			SCALE: NONE	CAD FILE: RE07U.SLDDRW
			SHEET 1 OF 1	