

**Bulk Cable Specification**

<b>MODEL</b>	<b>PRIMARY PACKAGING</b>	<b>SECONDARY PACKAGING</b>	<b>LENGTH (+ 10% / -0%)</b>
RG174-100	COIL	LOGO BAG	100 FT.
RG174-500	SPOOL	STRETCH WRAP, CARDBOARD, OR OTHER	500 FT.
RG174-1K	SPOOL	STRETCH WRAP, CARDBOARD, OR OTHER	1,000 FT.



50 OHM IMPEDANCE.

CENTER CONDUCTOR: 26 AWG. (7X34) BARE COPPER COVERED STEEL.

SHIELDING: TINNED COPPER BRAID (90% COVERAGE).

INSULATION: POLYETHYLENE.

JACKET: BLACK PVC.

OPERATING TEMPERATURE: -40°C - +75°C.

<b>NOMINAL ATTENUATION</b>		
<b>MHz</b>	<b>Db/100ft</b>	<b>Db/100m</b>
50	5.8	19.0
100	8.4	27.6
200	12.5	41.0
400	19.0	62.3
1,000	34.0	111.5

NOTE:

SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC