


Bulk Cable Specification

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
RG188A-100	COIL	LOGO BAG	100 FT.
RG188A-500	SPOOL	STRETCH WRAP	500 FT.
RG188A-1K	SPOOL	STRETCH WRAP	1,000 FT.



50 OHM IMPEDANCE.

CENTER CONDUCTOR: 26 AWG. (7X.0067) SILVER COATED
COPPER COVERED STEEL.

SHIELDING: SILVER COATED COPPER BRAID (96% SHIELD
COVERAGE).

INSULATION: TFE TEFLON.

JACKET: WHITE TFE TAPED.

OPERATING TEMPERATURE: -70°C - +200°C VW-1
VERTICAL FLAME TEST COMPLIANT.

NOMINAL ATTENUATION		
MHz	Db/100ft	Db/100m
50	9.4	30.8
100	10.4	34.1
200	13.2	43.3
400	16.5	54.1
1,000	31.0	101.7

NOTE:

1. SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC
2. MAY CONTAIN MORE THAN ONE PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50 FEET. 5 PIECE MAX PER 1000 FT.