


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/25/2002	C.MCCORMICK
B	REVISED CABLE DESCRIPTION (ECN1344)	03/25/03	MCCORMICK
.	.	.	.
.	.	.	.



PART NUMBER	LENGTH	
	METERS	FEET
SFOMU-01	1.0	3.3
SFOMU-02	2.0	6.6
SFOMU-03	3.0	9.8
SFOMU-04	4.0	13.1
SFOMU-05	5.0	16.4

- NOTES:
1. SINGLEMODE CONNECTOR ASSEMBLIES UTILIZE A PC POLISH.
 2. ALL CONNECTORS ACCOMPANIED WITH DUST CAP (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
 X ± .1
 .XX ± .05
 .XXX ± .005
 CABLE LENGTH TOLERANCE
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY MCCORMICK	08/06/02
CHECKED BY D.PARHAM	08/06/02
APPROVED BY R.CARRICK	08/06/02

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com CONNECTIVITY PRODUCTS
 45 BEECHWOOD DRIVE
 NORTH ANDOVER, MA
 01845

PRODUCT DESCRIPTION
MU FIBER OPTIC CABLE ASSEMBLIES

DRAWING TITLE
OUTLINE DRAWING

SIZE	FSCM NO.	DWG. NO.	REV.
A	43321	SFOMU-01-OD1	B
SCALE 1:2	CAD FILE: SFOMU-01-OD1.SLDDRW	SHEET 1 OF 1	