


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	01/19/01	MCCORMICK
B	REVISED TABLE ECN# 1128	06/11/02	MCCORMICK
.	.	.	.
.	.	.	.



2X ST STYLE CONNECTOR

9/125 SIMPLEX SINGLEMODE OFNR (RISER)  
O.D. 3mm, COLOR: YELLOW

PART NUMBER	LENGTH	
	METERS	FEET
SFOST-01	1.0	3.3
SFOST-02	2.0	6.6
SFOST-03	3.0	9.8
SFOST-04	4.0	13.1
SFOST-05	5.0	16.4



- NOTES:  
 1. SINGLEMODE CONNECTOR ASSEMBLIES UTILIZE PC POLISH.  
 2. ALL CONNECTORS ACCOMPANIED WITH DUST CAP (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:  
 .X ±.1  
 .XX ±.05  
 .XXX ±.005  
 CABLE LENGTH TOLERANCE  
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.McCORMICK	12/28/00
CHECKED BY	
DFP APPROVED BY	01/19/01
R.CARRICK	01/19/01

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

**L-com**<sup>®</sup> 45 BEECHWOOD DRIVE  
 CONNECTIVITY PRODUCTS NORTH ANDOVER, MA 01845

PRODUCT DESCRIPTION  
**9/125 SINGLEMODE FIBER**

DRAWING TITLE  
**OUTLINE DRAWING**

SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>SFOST-01-OD1</b>	REV. <b>B</b>
SCALE 1:2	CAD FILE SFOST-01-OD1.SLDDRW	SHEET 1	OF 1