


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/8/12	D.FRISIELLO
B	ECN6202: CHANGED RA BOOT FROM "LSZH" TO "PE"	6/11/12	D.DESJARDIN
C	ECN6551: UPDATED NOTES. CHANGED PE NOTE TO LSZH	12/28/12	D.DESJARDIN
D	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/21/14	D.FRISIELLO



WIRING MAP	
P1	P2
1	1 WHT/ORN
2	2 ORN
3	3 WHT/GRN
6	6 GRN
5	5 WHT/BLU
4	4 BLU
7	7 WHT/BRN
8	8 BRN


FOUR UNSHIELDED TWISTED PAIRS, CATEGORY 5E
24 AWG STRANDED COPPER
LOW SMOKE ZERO HALOGEN JACKET
SEE SHEET 2 OF 2 FOR COLOR



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS	DATE	L-com® Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D.FRISIELLO	1/26/12			
	CHECKED BY J.RUST	1/26/12	CATEGORY	TELECOM/MODULAR	
	APPROVED BY D.GALLAGHER	1/26/12	PRODUCT DESCRIPTION		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			C5E LSZ UTP STR-LFT		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRD815ZRA6	REV. D
		SCALE: NONE	CAD FILE: TRD815ZRA6.SLDDRW		SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815ZRA6BLK-1	BLACK	1.0 [0.30]	TRD815ZRA6RD-1	RED	1.0 [0.30]	TRD815ZRA6GRY-1	GRAY	1.0 [0.30]
TRD815ZRA6BLK-2	BLACK	2.0 [0.61]	TRD815ZRA6RD-2	RED	2.0 [0.61]	TRD815ZRA6GRY-2	GRAY	2.0 [0.61]
TRD815ZRA6BLK-3	BLACK	3.0 [0.91]	TRD815ZRA6RD-3	RED	3.0 [0.91]	TRD815ZRA6GRY-3	GRAY	3.0 [0.91]
TRD815ZRA6BLK-5	BLACK	5.0 [1.52]	TRD815ZRA6RD-5	RED	5.0 [1.52]	TRD815ZRA6GRY-5	GRAY	5.0 [1.52]
TRD815ZRA6BLK-7	BLACK	7.0 [2.13]	TRD815ZRA6RD-7	RED	7.0 [2.13]	TRD815ZRA6GRY-7	GRAY	7.0 [2.13]
TRD815ZRA6BLK-10	BLACK	10.0 [3.05]	TRD815ZRA6RD-10	RED	10.0 [3.05]	TRD815ZRA6GRY-10	GRAY	10.0 [3.05]
TRD815ZRA6BLK-15	BLACK	15.0 [4.57]	TRD815ZRA6RD-15	RED	15.0 [4.57]	TRD815ZRA6GRY-15	GRAY	15.0 [4.57]
TRD815ZRA6BLK-20	BLACK	20.0 [6.10]	TRD815ZRA6RD-20	RED	20.0 [6.10]	TRD815ZRA6GRY-20	GRAY	20.0 [6.10]
TRD815ZRA6BLK-25	BLACK	25.0 [7.62]	TRD815ZRA6RD-25	RED	25.0 [7.62]	TRD815ZRA6GRY-25	GRAY	25.0 [7.62]
TRD815ZRA6BLK-30	BLACK	30.0 [9.14]	TRD815ZRA6RD-30	RED	30.0 [9.14]	TRD815ZRA6GRY-30	GRAY	30.0 [9.14]



45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

C5E LSZ UTP STR-LFT

SIZE

A

FSCM NO.

43321

DWG. NO.

TRD815ZRA6

REV.

D

SCALE:

NONE

CAD FILE:

TRD815ZRA6.SLDDRW

SHEET 2 OF 2