

8 3 REVISIONS THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE REV DESCRIPTION DATE APPROVED WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED. ECN2917: UPDATED PICTORIALLY, UPDATED NOTE FORMAT AND CONTENT. 07/18/07 D.PARHAM ECN3191: ADDED 20, 30, 40, 60, 80 & 90 FT LENGTHS 02/06/08 D PARHAM ECN3320: ADDED PACKAGED ON A SPOOL NOTE, UPDATED FORMAT. 05/07/08 D. PARHAM ECN3552: ADDED RED & BLK CABLES. MODIFIED PACKAGING NOTE D. PARHAM LENGTH LENGTH LENGTH PART **JACKET** PA RT **JACKET** PART **JACKET** NUMBER COLOR NUMBER COLOR NUMBER COLOR **FEET METERS** FEET FEET **METERS METERS** TRD855DSZ-1 GRAY 1.0 TRD855DSZBLK-1 **BLACK** 1.0 TRD855DSZRD-1 RED 1.0 0.31 0.31 0.31 TRD855DSZ-2 GRAY 2.0 0.61 TRD855DSZBLK-2 20 TRD855DSZRD-2 RFD 20 0.61 BLACK 0.61 3.0 TRD855DSZ-3 GRAY 3.0 0.91 TRD855DSZBLK-3 **BLACK** 0.91TRD855DSZRD-3 RED 3.0 0.91 GRAY 5.0 5.0 TRD855DSZ-5 1.52 TRD855DSZBLK-5 **BLACK** 1.52 TRD855DSZRD-5 RED 5.0 1.52 TRD855DSZ-7 GRAY 7.0 2.13 TRD855DSZBLK-7 **BLACK** 7.0 2.13 TRD855DSZRD-7 RED 7.0 2.13 TRD855DSZ-10 GRAY 10.0 3.05 TRD855DSZBLK-10 **BLACK** 10.0 3.05 TRD855DSZRD-10 RED 10.0 3.05 TRD855DSZ-15 GRAY 15.0 4.57 TRD855DSZBLK-15 **BLACK** 15.0 4.57 TRD855DSZRD-15 RED 15.0 4.57 TRD855DSZ-20 GRAY 20.0 6.10 TRD855DSZBLK-20 **BLACK** 20.0 6.10 TRD855DSZRD-20 RED 20.0 6.10 TRD855DSZ-25 GRAY 25.0 7.62 TRD855DSZBLK-25 **BLACK** 25.0 7.62 TRD855DSZRD-25 RED 25.0 7.62 TRD855DSZ-30 GRAY 30.0 TRD855DSZBLK-30 30.0 TRD855DSZRD-30 RED 30.0 9.14 9.14 BLACK 9.14 12.19 TRD855DSZ-40 GRAY 40.0 12.19 TRD855DSZBLK-40 **BLACK** 40.0 TRD855DSZRD-40 RED 40.0 12.19 TRD855DSZ-50 GRAY 50.0 15.24 TRD855DSZBLK-50 **BLACK** 50.0 15.24 TRD855DSZRD-50 RED 50.0 15.24 TRD855DSZ-60 GRAY 60.0 18.29 TRD855DSZBLK-60 **BLACK** 60.0 18.29 TRD855DSZRD-60 RED 60.0 18.29 TRD855DSZ-75 GRAY 75.0 22.86 TRD855DSZBLK-75 **BLACK** 75.0 22.86 TRD855DSZRD-75 RED 75.0 22.86 TRD855DSZ-80 GRAY 24.38 TRD855DSZBLK-80 24.38 TRD855DSZRD-80 RED 80.0 BLACK 80.0 80.0 24.38 TRD855DSZ-90 GRAY 90.0 27.43 TRD855DSZBLK-90 **BLACK** 90.0 27.43 TRD855DSZRD-90 RED 90.0 27.43 TRD855DSZ-100 GRAY 100.0 30.48 TRD855DSZBLK-100 **BLACK** 100.0 30.48 TRD855DSZRD-100 RED 100.0 30.48 TRD855DSZ-150 GRAY 150.0 45.72 TRD855DSZBLK-150 **BLACK** 150.0 45.72 TRD855DSZRD-150 RED 150.0 45.72 TRD855DSZBLK-200 TRD855DSZ-200 GRAY 200.0 60.96 **BLACK** 200.0 60.96 TRD855DSZRD-200 RED 200.0 60.96 TRD855DSZ-250 GRAY 250.0 76.20 TRD855DSZBLK-250 250.0 76.20 TRD855DSZRD-250 RED 250.0 76.20 **BLACK GRAY** 300.0 300.0 TRD855DSZ-300 91.44 TRD855DSZBLK-300 **BLACK** 300.0 91.44 TRD855DSZRD-300 RED 91.44 45 BEECHWOOD DRIVE **APPROVALS** DATE UNLESS OTHERWISE SPECIFIED, -COM NORTH ANDOVER, MA DIMENSIONS ARE IN INCHES [mm] DRAWN BY CONNECTIVITY
PRODUCTS 01845 12/07/2006 D.PARHAM OVERALL CABLE LENGTH TOLERANCE: \$12 (305) = +1 (25) /-0 >12 (305) 560 11524 | +2 (51) /-0 >60 (1524) \$120 (3048) = +4 (102) /-0 >120 (3048) \$300 (7620) = +6 (152) /-0 >300 (7620) = +5% /-0% CATEGORY Α 12/07/2006 C.McCORMICK PROVED BY TELECOM/MODULAR D.GALLAGHER PRODUCT DESCRIPTION CONFIGURATION DETAILS OF ALL OTHER DIMENSIONAL TOLERANCES: UNDIMENSIONED FEATURES CATEGORY 5e PATCH CORD, LSZH MAY VARY .XX = .15**PROJECTION** FSCM NO DWG. NO. RFV COLOR VARIATIONS Ε 43321 TRD855DSZ MAY OCCUR

CAD FILE: TRD855DSZ.SLDDRW

SHEET 2 OF 2

SCALE: NONE

3

D

С

8

7