


# L-com offers Cable Options for every Application

## D-Subminiature


**Premium Lines:**  
CS2N, CS2NB, CS2H, CS2HB Series



### For High EMI/RFI Applications

- Double shielded cable (foil + braid)
- 360° full metal shell around backshell
- Gold plated contacts
- Metal thumbscrews that can be hand tightened


**Deluxe Lines:**  
CSMN, CSMNB, CHD Series



### Industry Standard

- Shielded cable (foil)
- 360° copper foil shield around backshell
- Gold plated contacts
- Metal thumbscrews that can be hand tightened

**Economy Line:**  
CSM Series



### Our Most Economical Solution

- Shielded cable (foil)
- 360° foil shield around backshell
- Gold flash contacts
- Slotted machine screws

## USB


**Premium Line:**  
CSMU Series



### For High Power Applications

- 20 AWG power conductors for max current
- Double shielded cable (foil + braid)
- 30μ gold plated contacts


**Deluxe Line:**  
CAUBLK Series



### For Medium Power Applications

- 24 AWG power conductors for medium current
- Double shielded cable (foil + braid)
- 30μ gold plated contacts

**Economy Line:**  
ECUSB Series




### Industry Standard

- 26 AWG power conductors
- Double shielded cable (foil + braid)
- 30μ gold plated contacts
- Eight off-the-shelf lengths

# Audio/Video

## VGA



### Premium Line: CTLF3VGA Series



#### For High EMI/RFI Applications

- Double shielded cable + steel box in backshell + molded ferrite cores for superior EMI/RFI protection

### Deluxe Lines: CTL3VGA, CTL3VGA-B (black) Series



#### For Medium EMI/RFI Applications

- Double shielded cable + steel box in backshell for increased EMI/RFI protection
- 45° versions available

### Economy Line: CGSVGA Series



#### Industry Standard

- Double shielded cable
- 360° copper foil shield in backshell
- Off-the-shelf lengths from 3-50 feet

## DVI

### Premium Lines: CTLDVI, CTLDVI-DL Series

#### For High EMI/RFI & Professional Video Applications

- 30μ gold plated contacts
- Angled versions available
- Ferrites for EMI/RFI protection
- Available in DVI-D and DVI-I variations



### Deluxe Lines: CGDVI, CGDVI-DL Series

#### Industry Standard

- Gold flash contacts
- Ferrites for EMI/RFI protection
- Fully molded backshells provide excellent strain relief




## HDMI

### Premium Line: HDCA Series

#### For Professional A/V Applications


- Six colors available
- 30μ gold plated contacts
- Angled versions available
- Support for Ethernet




### Deluxe Line: CGHD Series

#### Industry Standard

- Gold flash contacts
- Support for Ethernet
- Seven off-the-shelf lengths from 0.3m to 5m



## DIN and Mini DIN



### Premium Lines: DK226, DK238 Series

#### For High EMI/RFI Applications or Carrying Power

- Double shielded cable (foil + braid)
- 24AWG conductors
- Gold plated contacts
- Available only from L-com off-the-shelf



### Economy Lines: CSMD6, CSMD8 Series

#### Industry Standard

- Shielded cable (foil)
- 28AWG conductors
- Gold plated contacts

