

Major Equipment List – February 6, 2008

ASSET #	L-COM P/N	TOOL PART #	DESCRIPTION	S/N	VENDOR
300	C&PM-014	AMP854040-3	CRIMP&POKE MACHINE	854040-3	AMP
301	C&PM-015	SC750	CRIMP&POKE MACHINE	100.407	SCHLEUNIGER
302	FOS-001	FO 7010	FIBER OPTIC KEVLAR STRIPPER	112-99	SCHLEUNIGER
303	FOS-001	FO 7010	FIBER OPTIC KEVLAR STRIPPER	167-00	SCHLEUNIGER
304	FOS-001	FO 7010	FIBER OPTIC KEVLAR STRIPPER	168-00	SCHLEUNIGER
305	FOS-001	FO 7010	FIBER OPTIC KEVLAR STRIPPER	169-00	SCHLEUNIGER
306	FOS-002	FS 7030	FIBER OPTIC BUFFER STRIPPER	432	SCHLEUNIGER
307	FOS-002	FS 7030	FIBER OPTIC BUFFER STRIPPER	433	SCHLEUNIGER
308	FOS-002	FS 7030	FIBER OPTIC BUFFER STRIPPER	771	SCHLEUNIGER
309	FOS-002	FS 7030	FIBER OPTIC BUFFER STRIPPER	851	SCHLEUNIGER
310	FOS-003	FO 7045	FIBER OPTIC 3 STEP STRIPPER	190-1998	SCHLEUNIGER
311	FOP-001	APM-HDC-4000	FIBER OPTIC POLISHER	152H8980	DOMAILLE
312	FOP-001	APM-HDC-4000	FIBER OPTIC POLISHER	156H8980	DOMAILLE
313	FOP-001	APM-HDC-4000	FIBER OPTIC POLISHER	304H9921	DOMAILLE
314	FOP-001	APM-HDC-4000	FIBER OPTIC POLISHER	305H9921	DOMAILLE
315	FOP-001	APM-HDC-4000	FIBER OPTIC POLISHER	HDE2000	DOMAILLE
316	NC-007	PTA-100	PNEUMATIC MODULAR CRIMP MACHINE	12	STEWART
317	CCM-003	SCH-CT25	PNEUMATIC CRIMPER MACHINE	9717-1209	SCHLEUNIGER
318	CCM-012	AMP-904240-1	PNEUMATIC CRIMPER MACHINE		AMP
319	CCM-013	AMP-189722-1	PNEUMATIC CRIMPER MACHINE		AMP
320	CCM-014	AMP-189722-1	PNEUMATIC CRIMPER MACHINE		AMP
321	CCM-017	SCH-OC3950	CABLE CUTTING MACHINE	350	SCHLEUNIGER
322	CCM-017	SCH-OC3950	CABLE CUTTING MACHINE	1378-2000	SCHLEUNIGER
323	CCW-019	SCH-CP1250	CABLE COILER WRAPPER	255-1999	SCHLEUNIGER
324	CCW-019	SCH-CP1250	CABLE COILER WRAPPER	314-2000	SCHLEUNIGER
325	CFM-018	SCH-PF2000	CABLE PREFEEDER MACHINE	350	SCHLEUNIGER
326	CFM-018	SCH-PF2000	CABLE PREFEEDER MACHINE	1817	SCHLEUNIGER
327	ROM-015	B12A	REEL-O-MATIC MACHINE	1-118-2UM	REEL-NEAT SYSTEMS,INC
328	TWM-016	A-304	TIE WRAP MACHINE	2399	PETERS
329	CSM-012	SCH-US2500	SINGLE WIRE STRIPPER	532	SCHLEUNIGER
330	CSM-013	SCH-207	CABLE STRIPPER MACHINE	882	SCHLEUNIGER
331	CSM-013	SCH-207	CABLE STRIPPER MACHINE	2804	SCHLEUNIGER
332	CSM-014	JS8300	JACKET STRIPPING MACHINE	1156-2002	SCHLEUNIGER
333	CSM-015	MP257	CABLE STRIPPER MACHINE	5722	SCHLEUNIGER
334	CSM-016	MP257	CABLE STRIPPER MACHINE	6305	SCHLEUNIGER
335	CSM-017	US 2545	JACKET STRIPPING MACHINE	10102-00	SCHLEUNIGER
336	TST-001	1000R+	SIGNATURE ELECTRONIC TESTER	11317-R	CIRRIS
337	TST-002	1000R+	SIGNATURE ELECTRONIC TESTER	11306-R	CIRRIS
338	TST-003	1000R+	SIGNATURE ELECTRONIC TESTER	10522-R	CIRRIS
339	TST-004	1000R+	SIGNATURE ELECTRONIC TESTER	10523-R	CIRRIS
340	TST-005	1000R+	SIGNATURE ELECTRONIC TESTER	11034-R	CIRRIS
341	TST-006	1000R+	SIGNATURE ELECTRONIC TESTER	11292-R	CIRRIS
342	TST-007	1000R+	SIGNATURE ELECTRONIC TESTER	11276-R	CIRRIS
343	TST-008	S-90HV	HIGH VOLTAGE TESTER	1033	CABLESCAN
344	TST-009	LTS-3900	FIBER OPTIC LOSS TESTER	96589-2Z	EXFO

Major Equipment List – February 6, 2008

ASSET #	L-COM P/N	TOOL PART #	DESCRIPTION	S/N	VENDOR
345	TST-010	FM310-3MM	FIBER OPTIC POWER METER	P0915	FOTEC
346	TST-011	FM310-3MM	FIBER OPTIC POWER METER	P80861	FOTEC
347	TST-012	FS370/238	FIBER OPTIC POWER SOURCE	S80856	FOTEC
349	TST-013	FS370/238	FIBER OPTIC POWER SOURCE	S09100	FOTEC
350	TST-014	FV-200X	FIBER MICROSCOPE	√S99-40-1070	WESTOVER
351	TST-015	FV-400X	FIBER MICROSCOPE	√S99-41-1230	WESTOVER
352	TST-016	ME3200	MULTI-POWER MICROSCOPE	3200205	OPTISPEC
353	TST-017	OMEGA	MULTI-POWER MICROSCOPE	202061	OMEGA
354	USM-001	2510	ULTRASONIC CLEANER	060026362D	BRANSON
355	DPM-001	14-040	DRILL PRESS	8742	DELTA
356	DPM-002	105-1100	MILLING MACHINE	893398	ENCO
357	TST-018	1000R+	SIGNATURE ELECTRONIC TESTER	10322-R	CIRRUS
358	TST-019	1000R+	SIGNATURE ELECTRONIC TESTER	11033-R	CIRRUS
359	TST-020	N/A	VIDEO MICROSCOPE	219026	N/A
360	CCM-015	189722-1	PNEUMATIC CRIMP MACHINE	N/A	AMP
361	NC-007	PTA-100	PNEUMATIC CRIMP MACHINE	PTA-5001	STEWART
362	PF-001	PF-MTRJ-10	10 POS. MTRJ POLISHING PUCK	5425	DOMAILLE
363	PF-002	PF-FC-12	12 POS. FC POLISHING PUCK	2980	DOMAILLE
364		MP - 8015	JACKET STRIPPING MACHINE		SCHLEUNIGER
365		RSL 9500	CABLE PROCESSING MACHINE	267-1998	SCHLEUNIGER
366	PF-002	PF-FC-12	12 POS. FC POLISHING PUCK	3598	DOMAILLE
367	General	AMP - 626	PNEUMATIC CRIMPER		AMP
368	General	AMP - 626	PNEUMATIC CRIMPER		AMP
369	General	AMP - 626	PNEUMATIC CRIMPER		AMP
370	PF-003	PF-SC-12	12 POS. SC POLISHING PUCK	4330	DOMAILLE
371	PF-004	PF-LCF-12	12 POS. LCF POLISHING PUCK	5788	DOMAILLE
372	PF-004	PF-LCF-12	12 POS. LCF POLISHING PUCK	5940	DOMAILLE
373	General	AMP - 626	PNEUMATIC CRIMPER		AMP
374	PF-005	PF-ST-18	18 POS. ST POLISHING PUCK	5996	DOMAILLE
367	General	AMP	Pneumatic Crimpier		AMP
369	GENERAL	AMP	PNEUMATIC CRIMPER		AMP
372	GENERAL	AMP	PNEUMATIC CRIMPER		AMP
374	PH2003	DMC	Air over Hydraulic Crimp		DMC
377	GENERAL	FOCUS - LITE	AUTOMATIC HEAT SHRINK MACHINE		FOCUS - LITE
378	China	DMC	Bench Press		China
380		AMP	PNEUMATIC CRIMPER		AMP
381		AMP	PNEUMATIC CRIMPER		AMP
382	AT -016	Zengineering	Pneumatic Boot Set		Zengineering
383	H - T 8501	HO TIEN	AUTO-TERMINATION MODULAR MACH.	8501	HO TIEN
384	SS20NS	STEWART	CRIMPER / TESTER		STEWART
388	Y350C	Y350C	YUH - DAIK Y350 VERTICAL MOLDING	107020009-0	YUH - DAK
389	SMC	SMC	SMC PORTABLE CHILLER		STERLIN
390	SHD DRYER	DRYER	SHINI DRYER		SHINI