



HG2424G
STYLE
A
(Vertical)




HG2427G
STYLE
A



HG2430G
STYLE
B



HG915G-NF
STYLE
A
(Horizontal)



HG5421G
STYLE
A
(Vertical)

HG5421G
(Horizontal)



| Item # | Style | Description | 1-9 | 10-24 | 25-99 | 100-249 | 250-499 |
|--------|-------|-------------|-----|-------|-------|---------|---------|
|--------|-------|-------------|-----|-------|-------|---------|---------|

RoHS 2.4 GHz Grid Antennas

L-com's HyperLink® high performance reflector grid Wi-Fi antennas are available in gain ranges of 15 dBi to 30 dBi and are ideally suited for long-range highly directional applications. These applications include point to point systems, point to multipoint systems and wireless bridges in the 2.4 GHz ISM band as well as IEEE 802.11b/g/n wireless LAN systems. L-com's grid antennas can be installed for either vertical or horizontal polarization. Not all models are available in 5 packs.

- Wide range of frequencies
- Extensive selection of gain choices
- Point-to-point systems
- Point-to-multipoint systems
- Long-range directional applications
- RoHS compliant

| SOLD INDIVIDUALLY (NO 5-PACKS) | | | 1-9 | 10-24 | 25-99 | 100-249 | 250-499 |
|--------------------------------|---|---|--------|--------|--------|---------|---------|
| HG2415G-NM | A | 15 dBi, 12in Pigtail with NM Connector ANATEL Certified | 52.99 | 51.40 | 49.81 | 48.22 | 46.63 |
| HG2427G | A | 27 dBi, Integral NF Connector | 249.99 | 229.99 | 209.99 | 189.99 | 169.99 |
| HG2430G | B | 30 dBi, 18in Pigtail with NF Connector | 429.99 | 412.79 | 395.59 | 365.49 | 322.49 |
| HG2430G-NM | B | 30 dBi, 18in Pigtail with NM Connector | 479.99 | 451.19 | 422.39 | 393.59 | 364.79 |
| SOLD INDIVIDUALLY | | | 1-4 | 5-9 | 10-24 | 25+ | |
| HG2415G-NF | A | 15 dBi, 12in Pigtail with NF Connector | 36.99 | 36.62 | 36.25 | 35.88 | |
| HG2419G-NF | A | 19 dBi, 12in Pigtail with NF Connector | 44.99 | 44.54 | 44.09 | 43.64 | |
| HG2424G-NF | A | 24 dBi, 12in Pigtail with NF Connector | 57.99 | 57.41 | 56.83 | 56.25 | |
| HG2424G-NM | A | 24 dBi, 12in Pigtail with NM Connector | 59.99 | 59.39 | 58.79 | 58.19 | |
| 5-PACKS | | | 1-4 | 5-9 | 10-24 | 25+ | |
| HG2415G-NF-5PK | 1 | 15 dBi, 12in Pigtail with NF Connector, 5-Pack | 164.99 | 163.34 | 161.69 | 160.04 | |
| HG2419G-NF-5PK | 1 | 19 dBi, 12in Pigtail with NF Connector, 5-Pack | 205.99 | 199.81 | 193.63 | 187.45 | |
| HG2424G-NF-5PK | 1 | 24 dBi, 12in Pigtail with NF Connector, 5-Pack | 255.99 | 243.19 | 230.39 | 217.59 | |
| HG2424G-NM-5PK | 1 | 24 dBi, 12in Pigtail with NM Connector, 5-Pack | 259.99 | 246.99 | 233.99 | 220.99 | |

Tip Tilt and Swivel Mounting

The HG2430G antenna is supplied with a 60 degree tilt and swivel mast mount kit. This allows installation at various degrees of incline for easy alignment. Antenna alignment is critical to the system's operation between sites. This versatile mount aids the installer in the field to achieve better alignment accuracy, optimizing system performance for the user.



900 MHz, 5.4 GHz and 5.8 GHz Grid Antennas

L-com's HyperLink® grid antennas feature a multi-piece reflector grid. With this type of design they are not only easy to assemble, but it significantly reduces shipping costs compared to similar antennas with one piece reflector grid. All of our reflector grids are UV powder coated for durability and aesthetics and the open-frame design minimizes wind loading. Not all models are available in 5 packs.

- Superior performance
- Die cast aluminum construction
- All weather operation
- UV stable light gray powder coat finish
- 19° beam-width
- RoHS compliant

RoHS 900 MHz Grid Antennas

| SOLD INDIVIDUALLY (NO 5-PACKS) | | | 1-4 | 5-9 | 10-24 | 25+ |
|--------------------------------|---|--|--------|--------|--------|--------|
| HG918G-NF-2 | B | 18 dBi, 18in Pigtail with NF Connector | 327.99 | 314.87 | 301.75 | 288.63 |
| SOLD INDIVIDUALLY | | | 1-4 | 5-9 | 10-24 | 25+ |
| HG915G-NF | A | 15 dBi, 30in Pigtail with NF Connector | 73.99 | 73.25 | 72.51 | 71.77 |
| 5-PACKS | | | 1-4 | 5-9 | 10-24 | 25+ |
| HG915G-NF-5PK | A | 15 dBi, 30in Pigtail with NF Connector, 5-Pack | 337.99 | 327.85 | 317.71 | 307.57 |

RoHS 5.4 GHz Grid Antennas

| SOLD INDIVIDUALLY | | | 1-4 | 5-9 | 10-24 | 25+ |
|-----------------------------|---|---------------------------------------|--------|--------|--------|--------|
| HG5421G | A | 21 dBi, Integral NF Connector | 54.99 | 54.44 | 53.89 | 53.34 |
| HG5426G | A | 26 dBi, Integral NF Connector | 59.99 | 59.39 | 58.79 | 58.19 |
| 5-PACKS | | | 1-4 | 5-9 | 10-24 | 25+ |
| HG5421G-5PK | A | 21 dBi, Integral NF Connector, 5-Pack | 257.99 | 250.25 | 242.51 | 234.77 |
| HG5426G-5PK | A | 26 dBi, Integral NF Connector, 5-Pack | 259.99 | 252.19 | 244.39 | 236.59 |

RoHS 5.8 GHz Grid Antennas

| SOLD INDIVIDUALLY | | | 1-4 | 5-9 | 10-24 | 25+ |
|-----------------------------|---|--|--------|--------|--------|--------|
| HG5822G | A | 22 dBi, Integral NF Connector ANATEL Certified | 52.99 | 52.46 | 51.93 | 51.40 |
| HG5827G | A | 27 dBi, Integral NF Connector | 57.99 | 57.41 | 56.83 | 56.25 |
| 5-PACKS | | | 1-4 | 5-9 | 10-24 | 25+ |
| HG5822G-5PK | A | 22 dBi, Integral NF Connector, 5-Pack | 249.99 | 237.49 | 224.99 | 212.49 |
| HG5827G-5PK | A | 27 dBi, Integral NF Connector, 5-Pack | 267.99 | 259.95 | 251.91 | 243.87 |

See The Video www.L-com.com/Videos/A25

How to assemble and install a Grid Antenna

Two-piece grid antenna reflectors allow easy handling, shipping, and transportation to the site. Large grid antennas come in two symmetrical sections. They are bolted together on site easily, with feed then installed. See the online video for complete instructions at www.L-com.com/Videos/A25.

