



Item #	Style	Description	1-9	10-24	25-99	100-249	250-499
--------	-------	-------------	-----	-------	-------	---------	---------

**900 MHz, 1.9 GHz, 2.4 GHz and 5.8 GHz Yagi Antennas - Designed for Long Range Directional Operation**

These rugged outdoor rated directional Yagi antennas are ideally suited for IEEE 802.11b/g/n, PCS and 900 MHz ISM applications. HyperLink® offers both radome enclosed models as well as non-radome enclosed Yagi antennas. A multitude of gain and connector options are available. For a complete listing of HyperLink® Yagi antennas visit [www.L-com.com](http://www.L-com.com).

**✓RoHS 900 MHz Yagi Antennas**

HG903YE-NF	A	3 dBi, Aluminum, 15in Pigtail with NF Connector	24.99	22.49	19.99	17.49	14.99
HG906YE-NF	A	6 dBi, Aluminum, 15in Pigtail with NF Connector	27.99	25.19	22.39	19.59	16.79
HG909YE-NF	A	9 dBi, Aluminum, 15in Pigtail with NF Connector	31.99	28.79	25.59	22.39	19.19
HG912YE-NF	A	12 dBi, Aluminum, 15in Pigtail with NF Connector	33.99	30.59	27.19	23.79	20.39
HG914YE-NF	A	14 dBi, Aluminum, 15in Pigtail with NF Connector	41.99	37.79	33.59	29.39	25.19
HG909Y-NF	A	9 dBi, Stainless Steel, 18in Pigtail with NF Connector	31.99	30.71	29.43	27.19	23.99
HG909Y-NM	A	9 dBi, Stainless Steel, 18in Pigtail with NM Connector	45.99	44.15	42.31	39.09	34.49
HG913Y-NF	A	13 dBi, Stainless Steel, 18in Pigtail with NF Connector	47.99	46.07	44.15	40.79	35.99
HG913Y-NM	A	13 dBi, Stainless Steel, 18in Pigtail with NM Connector	59.99	57.59	55.19	50.99	44.99
HG914Y-NF	A	14 dBi, Aluminum, 12in Pigtail with NF Connector	119.99	115.19	110.39	101.99	89.99
HG914Y-NM	A	14 dBi, Aluminum, 12in Pigtail with NM Connector	134.99	129.59	124.19	114.74	101.24

**1.9 GHz Yagi Antenna**

HG1912SY-NF	A	12 dBi, Stainless Steel, 7in Pigtail with NF Connector	44.99	41.39	37.79	34.19	30.59
-------------	---	--	-------	-------	-------	-------	-------

**✓RoHS 2.4 GHz Yagi Antennas**

HG2409Y-NF	B	9 dBi, Radome Enclosed, 12in Pigtail with NF Connector	39.99	35.99	31.99	27.99	23.99
HG2409Y-NM	B	9 dBi, Radome Enclosed, 12in Pigtail with NM Connector	49.99	44.99	39.99	34.99	29.99
HG2412SY-NF	A	12 dBi, Stainless Steel, 7in Pigtail with NF Connector	44.99	41.39	37.79	34.19	30.59
HG2412Y-NF	B	12 dBi, Radome Enclosed, 12in Pigtail with NF Connector	44.99	40.49	35.99	31.49	26.99
HG2412Y-NM	B	12 dBi, Radome Enclosed, 12in Pigtail with NM Connector	54.99	49.49	43.99	38.49	32.99
HG2415Y-NF	B	14.5 dBi, Radome Enclosed, 12in Pigtail with NF Connector	44.99	41.39	37.79	34.19	30.59
HG2415Y-NM	B	14.5 dBi, Radome Enclosed, 12in Pigtail with NM Connector	44.99	41.39	37.79	34.19	30.59

**✓RoHS 2.4/5.8 GHz Log Periodic Antennas**

HG2458-08LP-NF	C	8 dBi, Radome Enclosed, 9in Pigtail with NF Connector	64.99	58.49	51.99	45.49	38.99
----------------	---	---	-------	-------	-------	-------	-------

**900 MHz, 1.2 GHz, 1.9 GHz and 2.4 GHz Range Extender Antennas**

HyperLink® range extender antennas can be used to achieve greater range than standard Rubber Duck antennas or a PC card's internal antenna. Full 360° coverage is provided by the Omni-Directional antennas and the Patch style range extender antennas feature directional operation. This series supports various applications including 2.4 GHz IEEE 802.11b/g/n wireless LANs, 800-1800 MHz ISM, GSM and RFID. Patch style antennas are designed for indoor use only and the Omni-Directional style range extenders can be used indoors or outdoors.

**✓RoHS 800/900 MHz Range Extender Antennas**

RE905U-SM	C	5 dBi, Integral MAG Mount Omni 4ft Cable SMA Male Connector	19.99	17.99	15.99	13.99	11.99
RE905U-TM	C	5 dBi, Integral MAG Mount Omni 4ft Cable TNC Male Connector	19.99	17.99	15.99	13.99	11.99
RE905U-RSP	C	5 dBi, Integral MAG Mount Omni 4ft Cable RP SMA Plug Connector	19.99	17.99	15.99	13.99	11.99
RE905U-NM	C	5 dBi, Integral MAG Mount Omni 4ft Cable N Male Connector	24.99	22.49	19.99	17.49	14.99

**✓RoHS 900/1800-1900 MHz Range Extender Antennas**

RE1903U-MC	C	3 dBi, Integral MAG Mount Omni 4ft Cable MC Card Connector	15.99	14.39	12.79	11.19	CALL
RE1903U-NM	C	3 dBi, Integral MAG Mount Omni 4ft Cable N Male Connector	22.99	20.69	18.39	16.09	13.79
RE1903U-SM	C	3 dBi, Integral MAG Mount Omni 4ft Cable SMA Male Connector	17.99	16.19	14.39	12.59	10.79
RE1903U-SNP	C	3 dBi, Integral MAG Mount Omni 4ft Cable SMA Nano Connector	15.99	14.39	12.79	11.19	CALL
RE1903U-TM	C	3 dBi, Integral MAG Mount Omni 4ft Cable TNC Male Connector	22.99	20.69	18.39	16.09	13.79

**✓RoHS 1.2 GHz Range Extender Antenna**

RE1208P-SM	E	8 dBi, 8in Square, 3ft Pigtail with SM Connector	29.99	28.49	26.99	25.49	CALL
------------	---	--	-------	-------	-------	-------	------

**✓RoHS 1.9 GHz Range Extender Antennas**

RE1905U-SM	A	5 dBi, Integral MAG Mount, 4ft Cable with SM Connector	19.99	17.99	15.99	13.99	11.99
RE1905U-SNP	A	5 dBi, Integral MAG Mount, 4ft Cable with SMA-Nano Connector	19.99	17.99	15.99	13.99	CALL

**✓RoHS 2.4 GHz Range Extender Antennas**

RE05ER-MC	B	5 dBi, 19in Cable with MC Connector	13.99	12.87	11.75	10.63	9.51
RE05ER-NM	B	5 dBi, 19in Cable with MMCX Connector	15.99	14.71	13.43	12.15	10.87
RE05ET-RSP	B	5 dBi, Integral MAG Mount, 4ft Cable with RP-SMA Connector	14.99	13.49	11.99	10.49	8.99
RE05U-MM	C	5 dBi, Integral MAG Mount, 4ft Cable with MMCX Connector	9.99	8.99	7.99	6.99	5.99
RE05U-RSP	C	5 dBi, Integral MAG Mount, 4ft Cable with RP-SMA Connector	9.99	8.99	7.99	6.99	5.99
RE05U-RTP	C	5 dBi, Integral MAG Mount, 4ft Cable with RP-TNC Connector	9.99	8.99	7.99	6.99	5.99
RE06P-RSP	E	6 dBi, 4in Square, 4ft Cable with RP-SMA Connector	26.99	24.83	22.67	20.51	18.35
RE06P-RTP	E	6 dBi, 4in Square, 4ft Cable with RP-TNC Connector	26.99	24.83	22.67	20.51	18.35
RE07U-MM	C	7 dBi, Integral MAG Mount, 4ft Cable with MMCX Connector	14.99	13.49	11.99	10.49	8.99
RE07U-RSP	C	7 dBi, Integral MAG Mount, 4ft Cable with RP-SMA Connector	14.99	13.49	11.99	10.49	8.99
RE07U-RTP	C	7 dBi, Integral MAG Mount, 4ft Cable with RP-TNC Connector	14.99	13.49	11.99	10.49	8.99
RE08P-RSP	A	8 dBi, 4in Round, 4ft Cable with RP-SMA Connector	31.99	28.79	25.59	22.39	19.19
RE08P-RTP	A	8 dBi, 4in Round, 4ft Cable with RP-TNC Connector	31.99	28.79	25.59	22.39	19.19
RE09U-RSP	D	8 dBi, Integral MAG Mount, 4ft Cable with RP-SMA Connector	59.99	56.39	52.79	49.19	45.59
RE09U-RTP	D	8 dBi, Integral MAG Mount, 4ft Cable with RP-TNC Connector	59.99	56.39	52.79	49.19	45.59
RE09P-RSP	E	8 dBi, 4in Square, 4ft Cable with RP-SMA Connector	29.99	26.99	23.99	20.99	17.99
RE09P-RTP	E	8 dBi, 4in Square, 4ft Cable with RP-TNC Connector	29.99	26.99	23.99	20.99	17.99
RE11DP-RSP	E	11 dBi, 8in Square, Dual Polarized, 3ft Cables with RP-SMA Connector	29.99	27.59	25.19	22.79	CALL
RE11DP-RTP	E	11 dBi, 8in Square, Dual Polarized, 3ft Cables with RP-TNC Connector	29.99	27.59	25.19	22.79	CALL
RE11DS-RSP	E	11 dBi, 8in Square, Dual Spacial, 3ft Cables with RP-SMA Connector	29.99	27.59	25.19	22.79	CALL
RE11DS-RTP	E	11 dBi, 8in Square, Dual Spacial, 3ft Cables with RP-TNC Connector	29.99	27.59	25.19	22.79	CALL
RE14P-RSP	E	14 dBi, 8in Square, 3ft Cable with RP-SMA Connector	34.99	31.49	27.99	24.49	CALL
RE14P-RTP	E	14 dBi, 8in Square, 3ft Cable with RP-TNC Connector	34.99	31.49	27.99	24.49	CALL

To see our full line of Range Extender Antennas go to [www.L-com.com](http://www.L-com.com).

