

**Parabolic Dish Antennas - Superior Strength Design Ensures Durability**

Our Wi-Fi parabolic dish antennas feature a high quality aluminum reflector dish for superior strength. The dish is coated in a light gray UV-inhibited polymer for durability and aesthetics. These directional dish antennas can be used in point to point as well as point to multipoint applications.

Built to withstand the elements, HyperLink® dish antennas offer high performance at competitive prices. When designing these Wi-Fi parabolic dish antennas, our design team factored in requirements such as location usage and environmental extremes. From versatile mounting options to features such as perforated reflectors, these antennas were built to withstand the test of time while maintaining optimal performance.


- Point-to-point systems
- Point-to-multipoint systems
- High quality aluminum construction
- All weather operation
- Many frequencies to choose from
- RoHS compliant



Item #	Style	Description	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS 2.4 GHz Dish Antennas</b>							
<a href="#">HG2414D</a>	D	14 dBi, 260mm Dia, Integral NF Connector	35.99	34.19	32.39	30.59	CALL
<b>✓RoHS 3.5 GHz Dish Antennas</b>							
<a href="#">HG3516D</a>	A	16 dBi, 246mm Dia, Integral NF Connector	49.99	45.99	41.99	37.99	CALL
<b>✓RoHS 4.9 GHz Dish Antennas</b>							
<a href="#">HG4931D</a>	B	30.5 dBi, 900mm Dia, Integral NF Connector	249.99	242.49	234.99	227.49	CALL
<b>✓RoHS 5.3 GHz Dish Antennas</b>							
<a href="#">HG5328D</a>	B	28 dBi, 600mm Dia, Integral NF Connector	167.99	162.95	157.91	152.87	CALL
<b>✓RoHS 5.4 GHz Dish Antennas</b>							
<a href="#">HG5423D</a>	B	23 dBi, 400mm Dia, Integral NF Connector	129.99	124.79	119.59	110.49	97.49
<a href="#">HG5428D</a>	B	28 dBi, 600mm Dia, Integral NF Connector	167.99	159.59	151.19	142.79	CALL
<a href="#">HG5432D</a>	B	32 dBi, 900mm Dia, Integral NF Connector	239.99	232.79	225.59	218.39	CALL
<b>✓RoHS 5.8 GHz Dish Antennas</b>							
<a href="#">HG5817D</a>	A	17 dBi, 246mm Dia, Integral NF Connector	41.99	39.89	37.79	35.69	CALL
<a href="#">HG5824D</a>	B	24 dBi, 400mm Dia, Integral NF Connector	137.99	132.47	126.95	117.29	103.49
<a href="#">HG5829D</a>	B	29 dBi, 600mm Dia, Integral NF Connector	169.99	161.49	152.99	144.49	CALL
<a href="#">HG5833D</a>	B	33 dBi, 900mm Dia, Integral NF Connector	254.99	247.34	239.69	232.04	CALL
<b>✓RoHS 5.1/5.8 GHz Broadband Dish Antennas</b>							
<a href="#">HG5158D</a>	C	30 dBi, Offset Feed, 830mm Dia, Integral NF Connector	157.99	153.25	148.51	143.77	CALL
<a href="#">HG5158DP-29D</a>	B	28.5 dBi, Dual Polarized, 600mm Dia, Integral NF Connector	259.99	246.99	233.99	220.99	CALL
<a href="#">HG5158DP-32D</a>	B	32 dBi, Dual Polarized, 900mm Dia, Integral NF Connector	339.99	322.99	305.99	288.99	CALL



**Parabolics available from 246mm to 900mm for all point-to-point applications.**



**✓RoHS Radome Cover Kits**


HyperLink® radome covers are an ideal way to provide additional protection to our parabolic dish antennas. These lightweight radome kits feature fiberglass construction and UV stable gray finish. Drain holes are provided on the radome cover to help prevent moisture build-up inside the dish antenna.

<a href="#">HGR-04</a>	Radome Cover Kit for 400mm Dia Dish	42.99	39.55	36.11	32.67	29.23
<a href="#">HGR-06</a>	Radome Cover Kit for 600mm Dia Dish	54.99	51.69	48.39	45.09	41.79
<a href="#">HGR-09</a>	Radome Cover Kit for 900mm Dia Dish	64.99	62.39	59.79	55.24	48.74



**Tip Easily attach a radome cover**

L-com's HyperLink® radome kits bolt directly to the dish antennas with the provided stainless steel hardware. Drilling mounting holes in the antenna is not required. The radome cover can be attached to existing antennas already mounted in the field or preassembled to the antenna before mounting.



Fiberglass Cover Kits - Protects against the elements.



To see our entire product offering go to...[www.L-com.com](http://www.L-com.com)