

Item #	Description	List Price
--------	-------------	------------

**EnGenius® Access Points/Routers/Bridges/Clients**

L-com now offers a broad line of EnGenius® access points, routers and wireless bridges. These products offer high power WLAN connectivity to 802.11 wireless Ethernet networks. Products range from standard 802.11b/g access points to feature rich, high power multi function solutions. For more detailed information and a complete listing of EnGenius® products visit our web site at [www.L-com.com](http://www.L-com.com).

**✓RoHS EnGenius® ECB Series Access Points**

With the quality and functionality expected of an EnGenius® product, the ECB Series provides up to 400mW of high wireless output power and also adds advanced features such as SNMP management, Wireless Distribution System (WDS), and Power-over-Ethernet (PoE) capability.

<a href="#">EN-ECB-3220</a>	EnGenius 802.11b/g Indoor Access Point	109.00
<a href="#">EN-ECB-3500</a>	EnGenius Multi Function 802.11b/g AP/Router/Bridge	109.00
<a href="#">EN-ECB-8610S</a>	EnGenius 802.11a/b/g AP/Bridge/WDS	109.00
<a href="#">EN-ECB-9500</a>	EnGenius Multi Function 802.11n AP/Router/Bridge	109.00

**✓RoHS EnGenius® EOC Series Access Points**

The EOC series brings superior range with its 400 mW high wireless output power, and the flexibility you need for adaptable deployments such as industrial grade outdoor enclosures, antenna options, and 802.3af Power-over-Ethernet (PoE) certification. Features such as 802.1x, WEP, and WPA2 provide high levels of security.

<a href="#">EN-EOC-1650</a>	EnGenius 802.11g Access Point/Client Bridge/Client Router	61.00
<a href="#">EN-EOC-2610</a>	EnGenius 802.11g Long Range Outdoor AP/Client Bridge	87.00
<a href="#">EN-EOC-5610</a>	EnGenius 802.11a/b/g Long Range Outdoor AP/Client Bridge	98.00
<a href="#">EN-EOC-3610S-EXT</a>	EnGenius 802.11b/g Maximum Range Outdoor AP/Client Bridge/WDS	164.00

**✓RoHS EnGenius® ESR Series 802.11g Mini Router**

The ESR-1221-EXT High-Power Long Range Wireless G Router supports home networking with superior throughput, performance, and unparalleled wireless range over standard Wireless G routers. High power gives it extended range to reach dead spots in your home or small office, offering great reliability and hassle free networking. The ESR-1221-EXT ships with a detachable SMA antenna which can be upgraded to a higher gain or directional antenna to expand the signal coverage where you need it. It features a built-in 4-port full-duplex 10/100 Fast Ethernet switch to connect your wired Ethernet devices together for seamless networking.

<a href="#">EN-ESR-1221-EXT</a>	EnGenius 802.11g Mini Router	41.00
---------------------------------	------------------------------	-------

**✓RoHS EnGenius® EAP Series "Smoke Detector" 802.11b/g Access Point**

The EAP-3660 is a smoke detector style Wireless Access Point/Universal Repeater that operates seamlessly in the 2.4 GHz frequency spectrum supporting the 802.11b (2.4 GHz, 11 Mbps) standard and SuperG 108 Mbps high speed networking. It's the best way to add wireless capability to your existing wired network or to add bandwidth to your wireless installation. The EAP-3660 features high wireless output power and receive sensitivity along with antenna diversity. High output power and high sensitivity extend wireless coverage to reduce the roaming between Access Points and to provide a reliable wireless connection. It also reduces the total cost of ownership on hardware.

<a href="#">EN-EAP-3660</a>	EnGenius 802.11b/g "Smoke Detector" Access Point	109.00
-----------------------------	--	--------

**✓RoHS EnGenius® EUB Series 802.11b/g High Power USB Adapter**

The EnGenius® EUB series USB WLAN adapters are designed for users who require maximum range and performance in their wireless networks. The EUB series offers a rich feature set including security features such as WPA and 802.1x.

<a href="#">EN-EUB-362-EXT</a>	EnGenius 802.11b/g High Power USB Adapter	42.00
<a href="#">EN-EUB-3701-EXT</a>	EnGenius 802.11g Dongle USB Adapter with External Antenna	29.00
<a href="#">EN-EUB-9701-EXT2</a>	EnGenius 802.11b/g/n High Power USB Adapter	39.00
<a href="#">EN-EUB-9702</a>	EnGenius 802.11n USB Adapter	21.00

**✓RoHS EnGenius® 802.11a/b/g Mini PCI Type III RF Module**

Having high output power is always a great bonus (up to 600 mW 28 dBm), when designing your embedded application. Introducing EnGenius® Technologies' answer, the EMP-8602S. Using the latest in technology expertise, EnGenius® has fine tuned the mini-PCI to be the longest, and most powerful RF module in the market today. The slim form factor allows for small physical applications. Your all-in-one solution encompassing 802.11a, 802.11b, and 802.11g networking technology will be the last mini-PCI high powered solution you will ever need.

<a href="#">EN-EMP-8602-PLUS-S</a>	EnGenius 802.11a/b/g Mini PCI Type III RF Module	59.00
<a href="#">EN-EMP-8603</a>	EnGenius 802.11a/b/g Mini PCI Type IIIA RF Module	76.00

**✓RoHS ALCON® 802.11a/b/g/n and Super G Wireless Access Points and MESH Radios**

The ALCON® 802.11 Access Point and MESH Radios provide the user and installer with a number of very versatile and powerful radios for installations where performance, range and coverage are challenging. These radios provide coverage for 2.4 GHz and 5.8 GHz frequency ranges in IEEE 802.11a/b/g/n and Super G, as specified by each radio. Most are PoE and come complete with everything needed for installation, excluding the antennas and cabling. Please call for the optimal HyperLink Antennas and Cabling to complete the installation. The power of each radio, when teamed with the correct antennas, provide extend range and wide area coverage. The ALCON® radios below are an excellent selection option for commercial and industrial applications and installation.

<a href="#">ALR-ASU-24005G-N</a>	WiFi AP/Bridge/Repeater 150 mW, 801.11b/g	359.00
<a href="#">ALR-ASU-5000-N</a>	WiFi AP/Bridge/Repeater 100 mW, 802.11a	575.00
<a href="#">ALR-APRO-2408G-N</a>	WiFi AP/Bridge/Repeater 800 mW, 801.11b/g	975.00
<a href="#">ALR-APPE-2408G-N</a>	WiFi AP/Bridge/Repeater 800 mW, 802.11b/g	875.00
<a href="#">ALR-AMESH-100</a>	WiFi MESH Network 100 mW	425.00
<a href="#">ALR-AMESH-500</a>	WiFi MESH Network 500 mW	625.00



**New**

EN-ECB-3220

[EN-ECB-3500](#)

[EN-EOC-3610S-EXT](#)

[EN-EOC-5610](#)

[EN-ESR-1221-EXT](#)

[EN-EAP-3660](#)

[EN-EUB-362-EXT](#)


[EN-EUB-3701-EXT](#)

[EN-EMP-8602-PLUS-S](#)

**New**

[EN-EMP-8603](#)

[ALR-ASU-24005G-N](#)



Detail view of the EN-EAP-3660

RJ45 Port with (802.3af PoE)  
DC Power - In

**Aesthetic "Smoke Detector" Design**

- Minimal footprint and no protruding antennas
- Designed to blend in to various business environments
- Unobtrusive design prevents tampering to protect your investment

**High 600mW Wireless Power**

- Ensures robust signal to overcome long distances
- Offers superior WiFi coverage than leading brands

**Multiple Wireless Names**

- Broadcasts multiple WiFi networks with one device
- Permits different levels of network access (VLAN Tagging)

**Power-over-Ethernet (802.3af Compliant)**

- Power and data over one cable to ease deployment



**Same day shipping**

Orders placed before 4:00 EST ship the same day.

