


RoHS Premium Category 5E RJ45 Molded Ethernet Patch Cords

Designed for today's high-density patch panels, these unique Category 5E molded patch cords feature an easy to depress "shark fin" snagless mold boot that makes connecting cables easier. The clear boot also allows the color of each cable to be easily seen to each port for easy cable identification. Each cable is tested for Category 5E performance to ensure maximum network throughput.

Category 5E Patch Cords



BL	BLK	GR	V	OR	R	GRY	Y	WHT
-----------	------------	-----------	----------	-----------	----------	------------	----------	------------

Ordering is easy, add the desired color code to the part number. Ex: TRD815BL-3

Item #	Description	Length	1-9	10-24	25-99	100-249	250-499
TRD815__-3	Category 5E Patch Cord, RJ45/RJ45	3.0 ft	3.99	3.59	3.19	2.79	2.39
TRD815__-5	Category 5E Patch Cord, RJ45/RJ45	5.0 ft	4.99	4.49	3.99	3.49	2.99
TRD815__-7	Category 5E Patch Cord, RJ45/RJ45	7.0 ft	5.99	5.39	4.79	4.19	3.59
TRD815__-10	Category 5E Patch Cord, RJ45/RJ45	10.0 ft	6.99	6.29	5.59	4.89	4.19
TRD815__-14	Category 5E Patch Cord, RJ45/RJ45	14.0 ft	8.99	8.09	7.19	6.29	5.39
TRD815__-25	Category 5E Patch Cord, RJ45/RJ45	25.0 ft	13.99	12.59	11.19	9.79	8.39
TRD815__-50	Category 5E Patch Cord, RJ45/RJ45	50.0 ft	24.99	22.49	19.99	17.49	14.99
TRD815__-75	Category 5E Patch Cord, RJ45/RJ45	75.0 ft	35.99	32.39	28.79	25.19	21.59
TRD815__-100	Category 5E Patch Cord, RJ45/RJ45	100.0 ft	46.99	42.29	37.59	32.89	28.19

10/100Base-T Crossover Patch Cords

TRD815CRY

TRD815CRBLK TRD815CRGR TRD815CRBL TRD815CRR

10/100Base-T Crossover Patch Cords

10Base-T Crossover

Tip *Network cable performance testing - be sure to choose the right cable for your needs*

Testing of cable assemblies is often an overlooked issue when it comes to Ethernet Patch Cords. A cable that uses Category 5E components may not really be Category 5E compliant. Economy grade cables are typically only tested for continuity whereas a certified patch cable is checked against the actual standard for performance criteria. Your level of requirement may not need a certified cable so if you are not sure give us a call and let us help you choose the perfect cable for your installation.

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
RoHS Premium Category 5E RJ45 Molded Crossover Ethernet Patch Cords							
TRD815CRBLK-3	10/100Base-T Crossover Patch Cord, 3.0 ft	Black	3.99	3.59	3.19	2.79	2.39
TRD815CRBLK-7	10/100Base-T Crossover Patch Cord, 7.0 ft	Black	5.99	5.39	4.79	4.19	3.59
TRD815CRBLK-10	10/100Base-T Crossover Patch Cord, 10.0 ft	Black	6.99	6.29	5.59	4.89	4.19
TRD815CRBLK-15	10/100Base-T Crossover Patch Cord, 15.0 ft	Black	8.99	8.09	7.19	6.29	5.39
TRD815CRGR-3	10/100Base-T Crossover Patch Cord, 3.0 ft	Green	3.99	3.59	3.19	2.79	2.39
TRD815CRGR-7	10/100Base-T Crossover Patch Cord, 7.0 ft	Green	5.99	5.39	4.79	4.19	3.59
TRD815CRGR-10	10/100Base-T Crossover Patch Cord, 10.0 ft	Green	6.99	6.29	5.59	4.89	4.19
TRD815CRGR-15	10/100Base-T Crossover Patch Cord, 15.0 ft	Green	8.99	8.09	7.19	6.29	5.39
TRD815CRBL-3	10/100Base-T Crossover Patch Cord, 3.0 ft	Blue	3.99	3.59	3.19	2.79	2.39
TRD815CRBL-7	10/100Base-T Crossover Patch Cord, 7.0 ft	Blue	5.99	5.39	4.79	4.19	3.59
TRD815CRBL-10	10/100Base-T Crossover Patch Cord, 10.0 ft	Blue	6.99	6.29	5.59	4.89	4.19
TRD815CRBL-15	10/100Base-T Crossover Patch Cord, 15.0 ft	Blue	8.99	8.09	7.19	6.29	5.39
TRD815CRR-3	10/100Base-T Crossover Patch Cord, 3.0 ft	Red	3.99	3.59	3.19	2.79	2.39
TRD815CRR-7	10/100Base-T Crossover Patch Cord, 7.0 ft	Red	5.99	5.39	4.79	4.19	3.59
TRD815CRR-10	10/100Base-T Crossover Patch Cord, 10.0 ft	Red	6.99	6.29	5.59	4.89	4.19
TRD815CRR-15	10/100Base-T Crossover Patch Cord, 15.0 ft	Red	8.99	8.09	7.19	6.29	5.39
TRD815CRY-3	10/100Base-T Crossover Patch Cord, 3.0 ft	Yellow	3.99	3.59	3.19	2.79	2.39
TRD815CRY-7	10/100Base-T Crossover Patch Cord, 7.0 ft	Yellow	5.99	5.39	4.79	4.19	3.59
TRD815CRY-10	10/100Base-T Crossover Patch Cord, 10.0 ft	Yellow	6.99	6.29	5.59	4.89	4.19
TRD815CRY-15	10/100Base-T Crossover Patch Cord, 15.0 ft	Yellow	8.99	8.09	7.19	6.29	5.39