




Unshielded Patch Cords




TRDU45




CATEGORY 5E  
• 2 pair 24 AWG stranded  
• PVC jacket




TRD450




CATEGORY 5E  
• 2 pair 24 AWG stranded  
• PVC jacket




TRD450CR




CATEGORY 5E  
• 2 pair 24 AWG stranded  
• PVC jacket




TRD855



CATEGORY 5E  
• 4 pair 24 AWG stranded  
• PVC jacket



TRD855PL



CATEGORY 5E  
• 4 pair 24 AWG solid  
• Plenum jacket

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

Unshielded Twisted Pair Patch Cords - Category 5E, For Most Network Environments

L-com offers the high quality Category 5E patch cords for use in today's rapidly changing network environments. Category 5E calls for 100 MHz bandwidth @ 100 Mbps data rate which is currently more than adequate for standard Ethernet environments. Unshielded assemblies are manufactured with UL Listed 24 AWG stranded cable with PVC jacket. Plugs have 50 microinches of gold; assemblies tested 100% prior to shipping.

**RoHS** Category 5E RJ11 to RJ11 Patch Cords - 2 Pair Stranded for 4 and 16 Mb Token Ring

<a href="#">TRDU45-2</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 2.0 ft	Beige	3.36	3.16	2.96	2.76	2.55
<a href="#">TRDU45-3</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 3.0 ft	Beige	3.60	3.38	3.17	2.95	2.74
<a href="#">TRDU45-5</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 5.0 ft	Beige	4.08	3.84	3.59	3.35	3.10
<a href="#">TRDU45-7</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 7.0 ft	Beige	4.56	4.29	4.01	3.74	3.47
<a href="#">TRDU45-10</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 10.0 ft	Beige	5.28	4.96	4.65	4.33	4.01
<a href="#">TRDU45-15</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 15.0 ft	Beige	6.48	6.09	5.70	5.31	4.92
<a href="#">TRDU45-25</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 25.0 ft	Beige	8.88	8.35	7.81	7.28	6.75
<a href="#">TRDU45-50</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 50.0 ft	Beige	14.88	13.99	13.09	12.20	11.31
<a href="#">TRDU45-100</a>	Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 100.0 ft	Beige	26.88	25.27	23.65	22.04	20.43

Twisted Pair Pinning: 2 & 5, 3 & 4.

**RoHS** Category 5E RJ45 to RJ45 Patch Cords - 2 Pair Stranded AWG24 for 10Base-T Ethernet

<a href="#">TRD450-2</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 2.0 ft	Beige	4.48	4.21	3.94	3.67	3.40
<a href="#">TRD450-3</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 3.0 ft	Beige	4.72	4.44	4.15	3.87	3.59
<a href="#">TRD450-5</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 5.0 ft	Beige	5.20	4.89	4.58	4.26	3.95
<a href="#">TRD450-7</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 7.0 ft	Beige	5.68	5.34	5.00	4.66	4.32
<a href="#">TRD450-10</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 10.0 ft	Beige	6.40	6.02	5.63	5.25	4.86
<a href="#">TRD450-15</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 15.0 ft	Beige	7.60	7.14	6.69	6.23	5.78
<a href="#">TRD450-25</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 25.0 ft	Beige	10.00	9.40	8.80	8.20	7.60
<a href="#">TRD450-50</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 50.0 ft	Beige	16.00	15.04	14.08	13.12	12.16
<a href="#">TRD450-100</a>	Cat. 5E 10Base-T Patch Cord, RJ45/RJ45, 100.0 ft	Beige	28.00	26.32	24.64	22.96	21.28

Twisted Pair Pinning: 1 & 2, 3 & 6.

**RoHS** Category 5E RJ45 to RJ45 Crossover Patch Cords - 2 Pair Stranded for Ethernet Hub Stacking


<a href="#">TRD450CR-2</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 2.0 ft	Beige	4.48	4.21	3.94	3.67	3.40
<a href="#">TRD450CR-3</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 3.0 ft	Beige	4.72	4.44	4.15	3.87	3.59
<a href="#">TRD450CR-5</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 5.0 ft	Beige	5.20	4.89	4.58	4.26	3.95
<a href="#">TRD450CR-7</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 7.0 ft	Beige	5.68	5.34	5.00	4.66	4.32
<a href="#">TRD450CR-10</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 10.0 ft	Beige	6.40	6.02	5.63	5.25	4.86
<a href="#">TRD450CR-15</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 15.0 ft	Beige	7.60	7.14	6.69	6.23	5.78
<a href="#">TRD450CR-25</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 25.0 ft	Beige	10.00	9.40	8.80	8.20	7.60
<a href="#">TRD450CR-50</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 50.0 ft	Beige	16.00	15.04	14.08	13.12	12.16
<a href="#">TRD450CR-100</a>	Cat. 5E 10Base-T Crossover Patch Cord, RJ45/RJ45, 100.0 ft	Beige	28.00	26.32	24.64	22.96	21.28

1 & 2, 3 & 6 Crossover allows Ethernet Hub Stacking.



**Tip** Which patch cords are best for a 10/100 Mbps Ethernet network?

Any of the TRD815 series patch cords found on page 34 will work effectively for ethernet networks. Choosing different colors for separate network segments in your wiring closet makes troubleshooting quick and easy.



**RoHS** Category 5E RJ45 to RJ45 Patch Cords - 4 Pair Stranded for 10Base-T, EIA568A and B Wiring

<a href="#">TRD855-1</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 1.0 ft	Beige	3.59	3.23	2.87	2.51	2.15
<a href="#">TRD855-2</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 2.0 ft	Beige	3.89	3.50	3.11	2.72	2.33
<a href="#">TRD855-3</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 3.0 ft	Beige	4.19	3.77	3.35	2.93	2.51
<a href="#">TRD855-5</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 5.0 ft	Beige	4.79	4.31	3.83	3.35	2.87
<a href="#">TRD855-7</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 7.0 ft	Beige	5.39	4.85	4.31	3.77	3.23
<a href="#">TRD855-10</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 10.0 ft	Beige	6.29	5.66	5.03	4.40	3.77
<a href="#">TRD855-15</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 15.0 ft	Beige	7.79	7.01	6.23	5.45	4.67
<a href="#">TRD855-25</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 25.0 ft	Beige	10.79	9.71	8.63	7.55	6.47
<a href="#">TRD855-50</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 50.0 ft	Beige	18.29	16.46	14.63	12.80	10.97
<a href="#">TRD855-100</a>	Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 100.0 ft	Beige	33.29	29.96	26.63	23.30	19.97

Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.

**RoHS** Category 5E RJ45 to RJ45 Plenum Patch Cords - 4 Pair Solid for EIA568A and B Wiring

<a href="#">TRD855PL-1</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 1.0 ft	Beige	11.99	11.75	11.27	10.55	8.99
<a href="#">TRD855PL-2</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 2.0 ft	Beige	12.49	12.24	11.74	10.99	9.37
<a href="#">TRD855PL-3</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 3.0 ft	Beige	12.99	12.73	12.21	11.43	9.74
<a href="#">TRD855PL-5</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 5.0 ft	Beige	13.99	13.71	13.15	12.31	10.49
<a href="#">TRD855PL-7</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 7.0 ft	Beige	15.49	15.18	14.56	13.63	11.62
<a href="#">TRD855PL-10</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 10.0 ft	Beige	16.99	16.65	15.97	14.95	12.74
<a href="#">TRD855PL-15</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 15.0 ft	Beige	19.99	19.59	18.79	17.59	14.99
<a href="#">TRD855PL-25</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 25.0 ft	Beige	25.99	25.47	24.43	22.87	19.49
<a href="#">TRD855PL-50</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 50.0 ft	Beige	40.99	40.17	38.53	36.07	30.74
<a href="#">TRD855PL-75</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 75.0 ft	Beige	55.99	54.87	52.63	49.27	41.99
<a href="#">TRD855PL-100</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 100.0 ft	Beige	70.99	69.57	66.73	62.47	53.24
<a href="#">TRD855PL-150</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 150.0 ft	Beige	100.99	98.97	94.93	88.87	75.74
<a href="#">TRD855PL-200</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 200.0 ft	Beige	130.99	128.37	123.13	115.27	98.24
<a href="#">TRD855PL-250</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 250.0 ft	Beige	160.99	157.77	151.33	141.67	120.74
<a href="#">TRD855PL-300</a>	Cat. 5E EIA568 Plenum Patch Cord, RJ45/RJ45, 300.0 ft	Beige	190.99	187.17	179.53	168.07	143.24

Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.

