


| Item # | Description | Color | 1-9 | 10-24 | 25-99 | 100-249 | 250-499 |
|--------|-------------|-------|-----|-------|-------|---------|---------|
|--------|-------------|-------|-----|-------|-------|---------|---------|

Shielded Category 5E Patch Cords with RJ45 (8x8) and RJ11 (6x4) Connectors

These screened (shielded) patch cords are great for use in electrically noisy environments where EMI is an issue. These assemblies utilize two or four pair cabling covered by a foil or foil+braided shield. Now available in flexible PVC and plenum jacket formulations. Assemblies are 100% tested and individually bagged.

Types of Shielded Cabling



JACKET TYPES:

- PVC - Non fire retardant, releases toxic gases when burned.
- LSZH - Fire retardant, greatly reduced toxic emissions when burned.
- Plenum - Fire retardant.

CONDUCTOR TYPES:

- Solid - Less flexible, can be punched into IDC connectors (110, 66, Krone).
- Stranded - Most flexible.

RoHS Category 5E Shielded RJ11 to RJ11 Patch Cords - 2 Pair USOC Wiring

| | | | | | | | |
|-------------------------------|---|-------|-------|-------|-------|-------|-------|
| TRDU45SCR-2 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 2.0 ft | Beige | 4.90 | 4.41 | 3.92 | 3.43 | 2.94 |
| TRDU45SCR-3 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 3.0 ft | Beige | 5.35 | 4.82 | 4.28 | 3.75 | 3.21 |
| TRDU45SCR-5 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 5.0 ft | Beige | 6.25 | 5.63 | 5.00 | 4.38 | 3.75 |
| TRDU45SCR-7 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 7.0 ft | Beige | 7.15 | 6.44 | 5.72 | 5.00 | 4.29 |
| TRDU45SCR-10 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 10.0 ft | Beige | 8.50 | 7.65 | 6.80 | 5.95 | 5.10 |
| TRDU45SCR-15 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 15.0 ft | Beige | 10.75 | 9.68 | 8.60 | 7.52 | 6.45 |
| TRDU45SCR-25 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 25.0 ft | Beige | 15.25 | 13.72 | 12.20 | 10.67 | 9.15 |
| TRDU45SCR-50 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 50.0 ft | Beige | 26.50 | 23.85 | 21.20 | 18.55 | 15.90 |
| TRDU45SCR-100 | Shielded Cat. 5E USOC-4 Patch Cord, RJ11/RJ11, 100.0 ft | Beige | 49.00 | 44.10 | 39.20 | 34.30 | 29.40 |

Twisted Pair Pinning: 2 & 5, 3 & 4.

RoHS Category 5E Shielded RJ45 to RJ45 Patch Cords - 4 Pair For EIA568A and B Wiring

| | | | | | | | |
|-------------------------------|---|----------|-------|-------|-------|-------|-------|
| TRD855SCR-1 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 1.0 ft | Lt. Gray | 7.69 | 7.07 | 6.46 | 5.84 | 5.23 |
| TRD855SCR-2 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 2.0 ft | Lt. Gray | 8.19 | 7.53 | 6.88 | 6.22 | 5.57 |
| TRD855SCR-3 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 3.0 ft | Lt. Gray | 8.79 | 8.09 | 7.38 | 6.68 | 5.98 |
| TRD855SCR-5 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 5.0 ft | Lt. Gray | 9.89 | 9.10 | 8.31 | 7.52 | 6.73 |
| TRD855SCR-7 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 7.0 ft | Lt. Gray | 10.99 | 10.11 | 9.23 | 8.35 | 7.47 |
| TRD855SCR-10 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 10.0 ft | Lt. Gray | 12.59 | 11.58 | 10.58 | 9.57 | 8.56 |
| TRD855SCR-15 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 15.0 ft | Lt. Gray | 15.39 | 14.16 | 12.93 | 11.70 | 10.47 |
| TRD855SCR-20 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 20.0 ft | Lt. Gray | 18.09 | 16.64 | 15.20 | 13.75 | 12.30 |
| TRD855SCR-25 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 25.0 ft | Lt. Gray | 20.89 | 19.22 | 17.55 | 15.88 | 14.21 |
| TRD855SCR-30 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 30.0 ft | Lt. Gray | 23.59 | 21.70 | 19.82 | 17.93 | 16.04 |
| TRD855SCR-40 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 40.0 ft | Lt. Gray | 29.09 | 26.76 | 24.44 | 22.11 | 19.78 |
| TRD855SCR-50 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 50.0 ft | Lt. Gray | 34.69 | 31.91 | 29.14 | 26.36 | 23.59 |
| TRD855SCR-75 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 75.0 ft | Lt. Gray | 48.39 | 44.52 | 40.65 | 36.78 | 32.91 |
| TRD855SCR-100 | Shielded Cat. 5E EIA568 Patch Cord, RJ45/RJ45, 100.0 ft | Lt. Gray | 62.19 | 57.21 | 52.24 | 47.26 | 42.29 |

Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.

RoHS Category 5E Shielded RJ45 to RJ45 Plenum Patch Cords - 4 Pair Solid for EIA568A & B Wiring

| | | | | | | | |
|-------------------------------|---|------|--------|--------|--------|--------|--------|
| TRD815SPL-1 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 1.0 ft | Blue | 24.99 | 24.49 | 23.49 | 21.99 | 18.74 |
| TRD815SPL-2 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 2.0 ft | Blue | 26.49 | 25.96 | 24.90 | 23.31 | 19.87 |
| TRD815SPL-3 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 3.0 ft | Blue | 27.99 | 27.43 | 26.31 | 24.63 | 20.99 |
| TRD815SPL-5 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 5.0 ft | Blue | 30.99 | 30.37 | 29.13 | 27.27 | 23.24 |
| TRD815SPL-7 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 7.0 ft | Blue | 33.99 | 33.31 | 31.95 | 29.91 | 25.49 |
| TRD815SPL-10 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 10.0 ft | Blue | 38.49 | 37.72 | 36.18 | 33.87 | 28.87 |
| TRD815SPL-15 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 15.0 ft | Blue | 45.99 | 45.07 | 43.23 | 40.47 | 34.49 |
| TRD815SPL-25 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 25.0 ft | Blue | 60.99 | 59.77 | 57.33 | 53.67 | 45.74 |
| TRD815SPL-50 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 50.0 ft | Blue | 98.49 | 96.52 | 92.58 | 86.67 | 73.87 |
| TRD815SPL-75 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 75.0 ft | Blue | 135.99 | 133.27 | 127.83 | 119.67 | 101.99 |
| TRD815SPL-100 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 100.0 ft | Blue | 173.49 | 170.02 | 163.08 | 152.67 | 130.12 |
| TRD815SPL-150 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 150.0 ft | Blue | 248.49 | 243.52 | 233.58 | 218.67 | 186.37 |
| TRD815SPL-200 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 200.0 ft | Blue | 323.49 | 317.02 | 304.08 | 284.67 | 242.62 |
| TRD815SPL-250 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 250.0 ft | Blue | 398.49 | 390.52 | 374.58 | 350.67 | 298.87 |
| TRD815SPL-300 | Shielded Cat. 5E Plenum Patch Cord, RJ45/RJ45, 300.0 ft | Blue | 473.49 | 464.02 | 445.08 | 416.67 | 355.12 |

Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.

RoHS Category 5E RJ45 to RJ45 Crossover Patch Cords

| | | | | | | | |
|-------------------------------|---|----------|-------|-------|-------|-------|-------|
| TRD855XCR-2 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 2.0 ft | Lt. Gray | 8.59 | 7.73 | 6.87 | 6.01 | 5.15 |
| TRD855XCR-3 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 3.0 ft | Lt. Gray | 9.19 | 8.27 | 7.35 | 6.43 | 5.51 |
| TRD855XCR-5 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 5.0 ft | Lt. Gray | 10.29 | 9.26 | 8.23 | 7.20 | 6.17 |
| TRD855XCR-7 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 7.0 ft | Lt. Gray | 11.39 | 10.25 | 9.11 | 7.97 | 6.83 |
| TRD855XCR-10 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 10.0 ft | Lt. Gray | 12.99 | 11.69 | 10.39 | 9.09 | 7.79 |
| TRD855XCR-15 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 15.0 ft | Lt. Gray | 15.79 | 14.21 | 12.63 | 11.05 | 9.47 |
| TRD855XCR-25 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 25.0 ft | Lt. Gray | 21.29 | 19.16 | 17.03 | 14.90 | 12.77 |
| TRD855XCR-50 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 50.0 ft | Lt. Gray | 34.99 | 31.49 | 27.99 | 24.49 | 20.99 |
| TRD855XCR-75 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 75.0 ft | Lt. Gray | 48.79 | 43.91 | 39.03 | 34.15 | 29.27 |
| TRD855XCR-100 | Cat. 5E Crossover Patch Cord, RJ45/RJ45, 100.0 ft | Lt. Gray | 62.49 | 56.24 | 49.99 | 43.74 | 37.49 |

Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.

Screened (Shielded) Patch Cords

TRDU45SCR

SHIELDED CATEGORY 5E

- 2 pair 26 AWG stranded
- PVC jacket
- Foil shielding

USOC-4

TRD855SCR

SHIELDED CATEGORY 5E

- 4 pair 26 AWG stranded
- PVC jacket
- Foil shielding

EIA568

TRD815SPL

SHIELDED CATEGORY 5E

- 4 pair 24 AWG solid
- Plenum rated
- Foil shielding

EIA568

TRD855XCR

SHIELDED CATEGORY 5E

- 4 pair crossover wired
- 26 AWG stranded conductors
- PVC jacket
- Foil shielding

10Base-T Crossover

Did you know...

Category 5E cables support Gigabit Ethernet (1000 Mbps) applications as defined by 802.3ab?