



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

M12 D-Coded 4 Position Cables for Ethernet and Fieldbus Applications

L-com now offers popular 22 AWG 2-pair, 4 Position, D-coded M12 cable assemblies for use in Ethernet and fieldbus applications. We stock multiple configurations including male to male, male to female and male (straight) to male (right angle), as well as male M12 to RJ45 plug styles. These robust assemblies are 100% factory tested and feature UV and chemical resistant PUR jackets. Applications for these assemblies include manufacturing, process control, factory automation and more. Contact us today with your custom M12 requirements.

✓RoHS M12 4 Position D-Coded Male to Male Cable Assemblies

M12M124D-0.5	M12 4 Position D-Coded Male/Male Cable Assembly, 0.5m	11.95	11.23	10.52	9.80	9.08
M12M124D-1	M12 4 Position D-Coded Male/Male Cable Assembly, 1.0m	12.95	12.17	11.40	10.62	9.84
M12M124D-2	M12 4 Position D-Coded Male/Male Cable Assembly, 2.0m	14.95	14.05	13.16	12.26	11.36
M12M124D-3	M12 4 Position D-Coded Male/Male Cable Assembly, 3.0m	16.95	15.93	14.92	13.90	12.88
M12M124D-5	M12 4 Position D-Coded Male/Male Cable Assembly, 5.0m	18.95	17.81	16.68	15.54	14.40

✓RoHS M12 4 Position D-Coded Male (Straight) to Male (Right Angle) Cable Assemblies

M12M12R4D-0.5	M12 4 Position D-Coded Male/Male Right Angle Cable Assembly, 0.5m	11.95	11.23	10.52	9.80	9.08
M12M12R4D-1	M12 4 Position D-Coded Male/Male Right Angle Cable Assembly, 1.0m	12.95	12.17	11.40	10.62	9.84
M12M12R4D-2	M12 4 Position D-Coded Male/Male Right Angle Cable Assembly, 2.0m	14.95	14.05	13.16	12.26	11.36
M12M12R4D-3	M12 4 Position D-Coded Male/Male Right Angle Cable Assembly, 3.0m	16.95	15.93	14.92	13.90	12.88
M12M12R4D-5	M12 4 Position D-Coded Male/Male Right Angle Cable Assembly, 5.0m	18.95	17.81	16.68	15.54	14.40

✓RoHS M12 4 Position D-Coded Male to Female Cable Assemblies

M12M12F4D-0.5	M12 4 Position D-Coded Male/Female Cable Assembly, 0.5m	13.95	13.11	12.28	11.44	10.60
M12M12F4D-1	M12 4 Position D-Coded Male/Female Cable Assembly, 1.0m	14.95	14.05	13.16	12.26	11.36
M12M12F4D-2	M12 4 Position D-Coded Male/Female Cable Assembly, 2.0m	16.95	15.93	14.92	13.90	12.88
M12M12F4D-3	M12 4 Position D-Coded Male/Female Cable Assembly, 3.0m	18.95	17.81	16.68	15.54	14.40
M12M12F4D-5	M12 4 Position D-Coded Male/Female Cable Assembly, 5.0m	21.95	20.63	19.32	18.00	16.68

✓RoHS M12 4 Position D-Coded Male to RJ45 Male Cable Assemblies

M12RJ454D-0.5	M12 4 Position D-Coded Male/RJ45 Male Cable Assembly, 0.5m	11.95	11.23	10.52	9.80	9.08
M12RJ454D-1	M12 4 Position D-Coded Male/RJ45 Male Cable Assembly, 1.0m	12.95	12.17	11.40	10.62	9.84
M12RJ454D-2	M12 4 Position D-Coded Male/RJ45 Male Cable Assembly, 2.0m	16.95	15.93	14.92	13.90	12.88
M12RJ454D-3	M12 4 Position D-Coded Male/RJ45 Male Cable Assembly, 3.0m	20.95	19.69	18.44	17.18	15.92
M12RJ454D-5	M12 4 Position D-Coded Male/RJ45 Male Cable Assembly, 5.0m	29.95	28.15	26.36	24.56	22.76

M12 A-Coded 5 Position Cables for Sensor and Fieldbus Applications

L-com stocks A-coded 5 Position M12 cable assemblies for use in sensor and fieldbus applications. These rugged cables feature PUR jackets, 22 AWG stranded conductors and are 100% factory tested to ensure system uptime.

✓RoHS M12 5 Position A-Coded Female to Cut End Cable Assemblies

M12FOE5A-0.5	M12 5 Position A-Coded Female/Cut End, 0.5m	8.95	8.41	7.88	7.34	6.80
M12FOE5A-1	M12 5 Position A-Coded Female/Cut End, 1.0m	10.25	9.63	9.02	8.41	7.79
M12FOE5A-2	M12 5 Position A-Coded Female/Cut End, 2.0m	12.95	12.17	11.40	10.62	9.84

✓RoHS M12 5 Position A-Coded Male to Male Cable Assemblies

M12M125A-0.5	M12 5 Position A-Coded Male/Male Cable Assembly, 0.5m	12.95	12.17	11.40	10.62	9.84
M12M125A-1	M12 5 Position A-Coded Male/Male Cable Assembly, 1.0m	14.95	14.05	13.16	12.26	11.36
M12M125A-2	M12 5 Position A-Coded Male/Male Cable Assembly, 2.0m	17.95	16.87	15.80	14.72	13.64
M12M125A-3	M12 5 Position A-Coded Male/Male Cable Assembly, 3.0m	20.95	19.69	18.44	17.18	15.92
M12M125A-5	M12 5 Position A-Coded Male/Male Cable Assembly, 5.0m	25.95	24.39	22.84	21.28	19.72

✓RoHS M12 5 Position A-Coded Male to Female Cable Assemblies

M12M12F5A-0.5	M12 5 Position A-Coded Male/Female Cable Assembly, 0.5m	14.95	14.05	13.16	12.26	11.36
M12M12F5A-1	M12 5 Position A-Coded Male/Female Cable Assembly, 1.0m	16.95	15.93	14.92	13.90	12.88
M12M12F5A-2	M12 5 Position A-Coded Male/Female Cable Assembly, 2.0m	19.95	18.75	17.56	16.36	15.16
M12M12F5A-3	M12 5 Position A-Coded Male/Female Cable Assembly, 3.0m	22.95	21.57	20.20	18.82	17.44
M12M12F5A-5	M12 5 Position A-Coded Male/Female Cable Assembly, 5.0m	28.95	27.21	25.48	23.74	22.00

