

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

### M12 D-Coded 4 Position and 5 Position Panel, PCB and Solder Style Connectors

L-com offers a complete line of D-Coded 4 and 5 Position M12 connectors for enclosure, panel and PCB applications. These quality constructed connectors provide years of trouble free use in the most trying applications. These M12 connectors are offered in both male and female versions and are rated to IP68.

#### ✓RoHS M12 D-Coded Panel Mount Connectors

<a href="#">CON-M124PM</a>	M12 4 Position Male Panel Mount Connector	7.50	7.35	7.20	7.05	6.90
<a href="#">CON-M125PM</a>	M12 5 Position Male Panel Mount Connector	7.95	7.79	7.63	7.47	7.31
<a href="#">CON-M124PF</a>	M12 4 Position Female Panel Mount Connector	8.25	8.08	7.92	7.75	7.59
<a href="#">CON-M125PF</a>	M12 5 Position Female Panel Mount Connector	8.95	8.77	8.59	8.41	8.23

#### ✓RoHS M12 D-Coded PCB Mount Connectors

<a href="#">CON-M124PCBM</a>	M12 4 Position Male PCB Mount Connector	6.95	6.81	6.67	6.53	6.39
<a href="#">CON-M125PCBM</a>	M12 5 Position Male PCB Mount Connector	7.25	7.10	6.96	6.81	6.67
<a href="#">CON-M124PCBF</a>	M12 4 Position Female PCB Mount Connector	9.95	9.75	9.55	9.35	9.15
<a href="#">CON-M125PCBF</a>	M12 5 Position Female PCB Mount Connector	10.95	10.73	10.51	10.29	10.07

#### ✓RoHS M12 D-Coded Solder Style Connectors

<a href="#">CON-M124SLDM</a>	M12 4 Position Male Solder Style Connector	7.95	7.79	7.63	7.47	7.31
<a href="#">CON-M125SLDM</a>	M12 5 Position Male Solder Style Connector	8.50	8.33	8.16	7.99	7.82
<a href="#">CON-M124SLDF</a>	M12 4 Position Female Solder Style Connector	9.95	9.75	9.55	9.35	9.15
<a href="#">CON-M125SLDF</a>	M12 5 Position Female Solder Style Connector	10.25	10.04	9.84	9.63	9.43

#### ✓RoHS M12 D-Coded 4 Position and 5 Position Adapters

L-com stocks a multitude of M12 D-Coded adapters including T style, I style and Y style M12 4 Position and 5 Position adapters. These rugged adapters are designed for use in harsh environments requiring temperature ranges from -25°C to 90°C.

#### ✓RoHS M12 D-Coded 3 Way T Style Adapters

<a href="#">ADPT-M124MT</a>	M12 4 Position 3 Way Male T Adapter	16.95	16.61	16.27	15.93	15.59
<a href="#">ADPT-M125MT</a>	M12 5 Position 3 Way Male T Adapter	18.25	17.88	17.52	17.15	16.79
<a href="#">ADPT-M124FT</a>	M12 4 Position 3 Way Female T Adapter	19.95	19.55	19.15	18.75	18.35
<a href="#">ADPT-M125FT</a>	M12 5 Position 3 Way Female T Adapter	22.25	21.80	21.36	20.91	20.47

#### ✓RoHS M12 D-Coded 2 Way I Style Adapters

<a href="#">ADPT-M124MI</a>	M12 4 Position Inline Male I Adapter	10.59	10.38	10.17	9.95	9.74
<a href="#">ADPT-M125MI</a>	M12 5 Position Inline Male I Adapter	11.59	11.36	11.13	10.89	10.66
<a href="#">ADPT-M124FI</a>	M12 4 Position Inline Female I Adapter	12.95	12.69	12.43	12.17	11.91
<a href="#">ADPT-M125FI</a>	M12 5 Position Inline Female I Adapter	14.50	14.21	13.92	13.63	13.34

#### ✓RoHS M12 D-Coded 3 Way Y Style Adapters

<a href="#">ADPT-M124MY</a>	M12 4 Position 3 Way Male Y Adapter	14.00	13.72	13.44	13.16	12.88
<a href="#">ADPT-M125MY</a>	M12 5 Position 3 Way Male Y Adapter	16.95	16.61	16.27	15.93	15.59
<a href="#">ADPT-M124FY</a>	M12 4 Position 3 Way Female Y Adapter	17.95	17.59	17.23	16.87	16.51
<a href="#">ADPT-M125FY</a>	M12 5 Position 3 Way Female Y Adapter	19.95	19.55	19.15	18.75	18.35

Item #	Description	List Price
--------	-------------	------------

#### ✓RoHS Hirschmann Field Attachable IP67 M12 Connector

This robust field attachable Industrial Ethernet M12 connector from Hirschmann is perfect for repair or installation of new and existing industrial cable plants. This connector is "D"-coded according to IEC 61076-2-101 4 and supports both 10Base-T and 100Base-T Ethernet applications. The EM12S Octopus is IP67 rated and features 4 contacts and IDC style termination.

<a href="#">EM12S OCTOPUS</a>	Hirschmann Field Attachable IP67 M12 Connector	26.95
-------------------------------	--	-------

#### ✓RoHS Hirschmann Bulkhead M12 to RJ45 IP67/65 Connector

This versatile IP67/65 adapter from Hirschmann provides a bulkhead style M12 connector on one and a shielded RJ45 jack on the other to address specific Industrial Ethernet applications. The M12 connector is "D"-coded according to IEC 61076-2-101 and supports both 10Base-T and 100Base-T Ethernet applications.

<a href="#">EF12RJ45 OCTOPUS</a>	Hirschmann Bulkhead M12 to RJ45 IP67/65 Connector	73.95
----------------------------------	---	-------

### M12 Adapter Configuration Options



T Style



I Style



Y Style




[CON-M125PF](#)  
Front View

[CON-M125PF](#)  
Back View



[CON-M124PCBF](#)  
Front View

[CON-M124PCBF](#)  
Back View



[CON-M124SLDF](#)  
Front View

[CON-M124SLDF](#)  
Back View



[ADPT-M125MT](#)



[ADPT-M124MI](#)



[ADPT-M124MY](#)



Front View

Back View

[EM12S OCTOPUS](#)



[EF12RJ45 OCTOPUS](#)



To see our entire product offering  
go to...[www.L-com.com](http://www.L-com.com)