




WT6788D
Front and Rear View



WT6788FS
Front and Rear View



WT6700FM
Front and Rear View



WT67KC5F



WT671105RM



WT67PC



WT67PCT



WT67RC



TRD855WTG

Item #	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS	Ruggedized IP67 Rated RJ45 Ethernet Plug Kit					
WT6788D	Non-Shielded Dome Style	19.95	19.15	18.35	17.56	16.76
WT6788F	Non-Shielded Flex Style	19.95	19.15	18.35	17.56	16.76
WT6788DS	Shielded Dome Style	22.95	22.03	21.11	20.20	19.28
WT6788FS	Shielded Flex Style	22.95	22.03	21.11	20.20	19.28
TSP4088C5	Replacement RJ45 Non-Shielded Plugs, Pkg/50	29.95	27.55	25.16	22.76	CALL
TSP4088C5S	Replacement RJ45 Shielded Plugs, Pkg/50	49.95	45.95	41.96	37.96	CALL

✓RoHS	Ruggedized IP67 Rated Keystone Flange Adapter Kits					
WT6700FM	Front Mount Empty	17.95	17.23	16.51	15.80	15.08
WT6700RM	Rear Mount Empty	17.95	17.23	16.51	15.80	15.08
WT67KC5F	Front Mount C5E Coupler	24.95	23.95	22.95	21.96	20.96
WT67KC5R	Rear Mount C5E Coupler	24.95	23.95	22.95	21.96	20.96
WT671105FM	Front Mount C5E IDC 110 Jack	19.95	19.15	18.35	17.56	16.76
WT671105RM	Rear Mount C5E IDC 110 Jack	19.95	19.15	18.35	17.56	16.76

✓RoHS	Protective Covers for WT67 Series Plugs and Jacks					
WT67RC	IP67 Jack Cover for Female Receptacles	5.95	5.71	5.47	5.24	5.00
WT67RCT	IP67 Jack Cover for Female Receptacles with Tether	10.95	10.51	10.07	9.64	9.20
WT67PC	IP67 Jack Cover for Male Plug Kits	6.95	6.67	6.39	6.12	5.84
WT67PCT	IP67 Jack Cover for Male Plug Kits with Tether	8.95	8.59	8.23	7.88	7.52

✓RoHS	Category 5E Outdoor Cables with Weather Tight Grommet					
TRD855WTG-5	Category 5E Outdoor Patch Cable with Weathertight Grommets, 5.0 ft	41.75	39.24	36.74	34.23	31.73
TRD855WTG-10	Category 5E Outdoor Patch Cable with Weathertight Grommets, 10.0 ft	44.75	42.06	39.38	36.70	34.01
TRD855WTG-25	Category 5E Outdoor Patch Cable with Weathertight Grommets, 25.0 ft	53.75	50.52	47.30	44.08	40.85
TRD855WTG-50	Category 5E Outdoor Patch Cable with Weathertight Grommets, 50.0 ft	68.75	64.63	60.50	56.38	52.25
TRD855WTG-100	Category 5E Outdoor Patch Cable with Weathertight Grommets, 100.0 ft	98.75	92.82	86.90	80.98	75.05

Tip

Easily attach a field installable plug

STEP 1

STEP 2

STEP 3

STEP 4

Industrial Category 5E Field Installable Connectors (Exploded View)

Compact Dome Cable Entry

Quick Latching Housing

Available with Shielded or Non-Shielded Plug

Gasket Seal for IP67 Rating

Flexible Cable Entry

Quick Latching Housing

Available with Shielded or Non-Shielded Plug

Gasket Seal for IP67 Rating

"I think L-com has a good variety of quality vs. cost products. We will be ordering again and have recommended L-com to other people."
- Rex Allen, Project Manager, Intelligent Access Systems of North Carolina