

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

Premium Category 6 RJ45 - 110 Keystone Jack - 90 Degree Style

Hellermann-Tyton's Gigaband™ Category 6 modular jack designed to "future proof" installations. Its patented design uses innovative crosstalk cancellation technology. The performance of the Gigaband system exceeds Category 6 and Class E requirements. These jacks will easily support emerging applications such as Gigabit Ethernet and 622 Mbps ATM. The 90° design has the 110 connectors at right angles to the modular plug. Comes in colors of Black, Blue, Brown, Office White, Green, Gray, Ivory, Orange, Red, Violet, White and Yellow.

Category 6 Keystone Jack, 110/RJ45 (8x8), EIA568A/B

UJ110C6-BLK	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Black	7.95	7.63	7.31	7.00	CALL
UJ110C6-BLU	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Blue	7.95	7.63	7.31	7.00	CALL
UJ110C6-BRN	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Brown	7.95	7.63	7.31	7.00	CALL
UJ110C6-FW	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Office White	7.95	7.63	7.31	7.00	CALL
UJ110C6-GRN	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Green	7.95	7.63	7.31	7.00	CALL
UJ110C6-GRY	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Gray	7.95	7.63	7.31	7.00	CALL
UJ110C6-I	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Ivory	7.95	7.63	7.31	7.00	CALL
UJ110C6-ORN	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Orange	7.95	7.63	7.31	7.00	CALL
UJ110C6-RED	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Red	7.95	7.63	7.31	7.00	CALL
UJ110C6-VIO	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Violet	7.95	7.63	7.31	7.00	CALL
UJ110C6-W	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	White	7.95	7.63	7.31	7.00	CALL
UJ110C6-YEL	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Yellow	7.95	7.63	7.31	7.00	CALL

Premium Category 5E RJ45 - 110 Keystone Jack - 90 Degree Style

Hellermann-Tyton Megaband™ Category 5E flush modular jacks are designed to meet the needs of end users and installers. These jacks will support Gigabit Ethernet and 622 Mbps ATM applications.

UJ110C5E-BLK	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Black	5.95	5.71	5.47	5.24	CALL
UJ110C5E-BLU	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Blue	5.95	5.71	5.47	5.24	CALL
UJ110C5E-BRN	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Brown	5.95	5.71	5.47	5.24	CALL
UJ110C5E-FW	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Office White	5.95	5.71	5.47	5.24	CALL
UJ110C5E-GRN	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Green	5.95	5.71	5.47	5.24	CALL
UJ110C5E-GRY	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Gray	5.95	5.71	5.47	5.24	CALL
UJ110C5E-I	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Ivory	5.95	5.71	5.47	5.24	CALL
UJ110C5E-ORN	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Orange	5.95	5.71	5.47	5.24	CALL
UJ110C5E-RED	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Red	5.95	5.71	5.47	5.24	CALL
UJ110C5E-VIO	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Violet	5.95	5.71	5.47	5.24	CALL
UJ110C5E-W	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	White	5.95	5.71	5.47	5.24	CALL
UJ110C5E-YEL	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Yellow	5.95	5.71	5.47	5.24	CALL

Category 5E RJ45 - 110 Keystone Jack - Traditional 180 Degree Style

The traditional 180° design has the 110 connectors parallel to the modular plug entry. This jack comes in Ivory and is EIA568A/B dual color coded.

RJ110C5B-I	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Ivory	5.95	5.83	5.71	5.59	5.47
----------------------------	---	-------	------	------	------	------	------

RoHS Category 5E RJ45 - 110 Shielded Keystone Jack - 180 Degree Style

This jack is similar to the RJ110C5 series except it is fully shielded for areas where noise is prevalent. Accepts EIA568A or B wiring.

RJ110C5-S	Cat. 5E Shld. Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Silver	8.95	8.77	8.59	8.41	8.23
---------------------------	---	--------	------	------	------	------	------

RoHS 10 Position Category 5 and USOC - 110 IDC Keystone Jacks - Traditional 180 Degree Style


These 10 position 10 contact keystone style jacks are an ideal solution in applications where additional contacts are required. The traditional 180° design has the 110 connectors parallel to the modular plug entry. Category 5 version is dual color coded, compatible with EIA568A and B wiring with position 1 and 10 populated.

EC1107B-USOC	Keystone IDC - 10P10C Jack, USOC	Black	6.95	6.67	6.39	6.12	CALL
EC1107B-10C5	Keystone IDC - 10P10C Jack, Cat. 5-568A/B	Black	6.95	6.67	6.39	6.12	CALL

RoHS Miscellaneous Keystone Jacks - Coaxial, Fiber and Audio/Video Couplers

Add more than just data and telephone connections to workstation outlets. L-com features audio, video, fiber and RF adapters designed to fit our wall plate systems.

MJSCPF-WT	Keystone Coaxial Type F Coupler Insert	White	1.45	1.30	1.16	1.01	0.87
MJSCPRCA-I	Keystone RCA Coupler Insert	White	2.45	2.21	1.96	1.72	1.47
MJSCPSC-WT	Keystone Fiber SC Coupler Insert	White	5.95	5.36	4.76	4.17	3.57
MJSCPST-WT	Keystone Fiber ST Coupler Insert	White	5.95	5.36	4.76	4.17	3.57
MJSCPBK-WT	Keystone Blank Insert	White	0.35	0.32	0.28	0.24	0.21
MJSCPF-IV	Keystone Coaxial Type F Coupler Insert	Ivory	1.45	1.30	1.16	1.01	0.87
MJSCPRCA-IV	Keystone RCA Coupler Insert	Ivory	2.45	2.21	1.96	1.72	1.47
MJSCPBNC-IV	Keystone BNC Coupler Insert	Ivory	2.45	2.21	1.96	1.72	1.47
MJSCPSC-IV	Keystone Fiber SC Coupler Insert	Ivory	5.95	5.36	4.76	4.17	3.57
MJSCPST-IV	Keystone Fiber ST Coupler Insert	Ivory	5.95	5.36	4.76	4.17	3.57
MJSCPBK-IV	Keystone Blank Insert	Ivory	0.35	0.32	0.28	0.24	0.21



Free access to over 3,000 CAD models
 Download CAD models and 2D drawings for integrating into your projects. L-com.com/CadDemo