

Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS</b>	<b>Crimp &amp; Poke Contacts - Choose Pins or Sockets, Flash or 30µ</b>					
<a href="#">CPM10</a>	Crimp & Poke Male Pins - Gold Flash, Pkg/10	2.50	2.30	2.10	1.90	1.70
<a href="#">CPM100</a>	Crimp & Poke Male Pins - Gold Flash, Reel/100	15.00	13.80	12.60	11.40	10.20
<a href="#">CPM100-30U</a>	Crimp & Poke Male Pins - 30µ Gold, Pkg/10	3.25	2.99	2.73	2.47	2.21
<a href="#">CPM100-30U</a>	Crimp & Poke Male Pins - 30µ Gold, Reel/100	19.50	17.94	16.38	14.82	13.26
<a href="#">CPF10</a>	Crimp & Poke Female Sockets - Gold Flash, Pkg/10	3.00	2.76	2.52	2.28	2.04
<a href="#">CPF100</a>	Crimp & Poke Female Sockets - Gold Flash, Reel/100	18.00	16.56	15.12	13.68	12.24
<a href="#">CPF100-30U</a>	Crimp & Poke Female Sockets - 30µ Gold, Pkg/10	3.75	3.45	3.15	2.85	2.55
<a href="#">CPF100-30U</a>	Crimp & Poke Female Sockets - 30µ Gold, Reel/100	22.50	20.70	18.90	17.10	15.30

**✓RoHS Insertion/Extraction Tools for Crimp & Poke Type Contacts - Professional and Economy Versions**

Two insertion/extraction tools are available for inserting contacts into D-Subs. Professional model is made for multiple insertions and is built on a larger, more ergonomic tool body. The economy version is also available when limited insertions are necessary.

<a href="#">TDI</a>	Economy Contact Insertion/Extraction Tool	2.95	2.71	2.48	2.24	CALL
<a href="#">TDTPRO</a>	Professional Contact Insertion/Extraction Tool	19.95	19.15	18.35	17.56	CALL

**D-Subminiature Contact Crimp Tool - For Crimp & Poke Series Pins and Sockets**

Professional grade tool crimps D-Subminiature pins and sockets for 20-30 AWG wires. Spring loaded holding mechanism centers and holds pin in place until crimping cycle is complete. Highest quality. See the Tip on page 88 for crimping instructions.

<a href="#">CP3127CT</a>	D-Sub Contact Crimp Tool	120.00	112.80	105.60	98.40	CALL
--------------------------	--------------------------	--------	--------	--------	-------	------

**D-Sub Hood Covers - Offering a Better Selection for Your Varied Cable Making Needs**

L-com offers a better selection of D-Sub hoods than ever before. We've discovered in our own cable production that needs are varied because users are more demanding in style selection than traditional plastic or metal hoods. They are supplied as kits with appropriate hardware for male mating. Order hex standoffs separately for female adaptation.

**✓RoHS Plastic D-Sub Hoods - Features One Piece Foldover Hinge Design**

One piece unshielded hoods are available for DB9, DB15, DB25 and DB50 sizes. They are constructed of Black plastic with long knurled thumbscrews. They feature a side snap lock for connector security and metal screw down strain relief. Attractive appearance.

<a href="#">SD121-09</a>	Hinged Hood Kit, DB9 Black	1.45	1.33	1.22	1.10	0.99
<a href="#">SD121-15</a>	Hinged Hood Kit, DB15 Black	1.55	1.43	1.30	1.18	1.05
<a href="#">SD121-25</a>	Hinged Hood Kit, DB25 Black	1.65	1.52	1.39	1.25	1.12
<a href="#">SD121-50</a>	Hinged Hood Kit, DB50 Black	2.05	1.89	1.72	1.56	1.39

**✓RoHS Metalized Plastic D-Sub Hoods - Low Profile and Contemporary Style and Finish**

These hoods are offered in three basic sizes, in attractive matte metalized (shielded) finish. Well constructed with metal strain relief bar, two screw closure and long knurled thumbscrews.

<a href="#">SDRS09HO</a>	Assembled Hood Kit, DB9 Matte Chrome	1.90	1.75	1.60	1.44	1.29
<a href="#">SDRS15HO</a>	Assembled Hood Kit, DB15 Matte Chrome	2.00	1.84	1.68	1.52	1.36
<a href="#">SDRS25HO</a>	Assembled Hood Kit, DB25 Matte Chrome	2.10	1.93	1.76	1.60	1.43

**✓RoHS Plastic Hoods - Mate with D-Subminiature Connectors for Cabling**

Molded plastic hoods are made of flame retardant materials. The metalized version is chrome plated providing conductivity and an RFI/EMI shield. A cable strain relief is also included.

<a href="#">SDC9G</a>	Assembled Hood Kit, DB9 Gray	0.85	0.78	0.71	0.65	0.58
<a href="#">SDC15G</a>	Assembled Hood Kit, DB15 Gray	1.00	0.92	0.84	0.76	0.68
<a href="#">SDC25G</a>	Assembled Hood Kit, DB25 Gray	1.05	0.97	0.88	0.80	0.71
<a href="#">SDC37G</a>	Assembled Hood Kit, DB37 Gray	1.20	1.10	1.01	0.91	0.82
<a href="#">SDC9B</a>	Assembled Hood Kit, DB9 Black	0.90	0.83	0.76	0.68	0.61
<a href="#">SDC15B</a>	Assembled Hood Kit, DB15 Black	1.05	0.97	0.88	0.80	0.71
<a href="#">SDC25B</a>	Assembled Hood Kit, DB25 Black	1.10	1.01	0.92	0.84	0.75
<a href="#">SDC9M</a>	Assembled Hood Kit, DB9 Metalized Chrome	1.05	0.97	0.88	0.80	0.71
<a href="#">SDC15M</a>	Assembled Hood Kit, DB15 Metalized Chrome	1.25	1.15	1.05	0.95	0.85
<a href="#">SDC25M</a>	Assembled Hood Kit, DB25 Metalized Chrome	1.35	1.24	1.13	1.03	0.92

**✓RoHS D-Sub Metal Hood Kits - Choice of Five Grommets to Satisfy all Size Requirements**

Cast alloy metal construction with a matte chrome plate finish over tin and copper for the best conductivity. Kit includes a set of five grommets and 4-40 thread mounting screws.

<a href="#">SDC9AG</a>	Assembled Hood Kit, DB9 Metal	2.50	2.35	2.20	2.05	1.90
<a href="#">SDC15AG</a>	Assembled Hood Kit, DB15 Metal	3.50	3.29	3.08	2.87	2.66
<a href="#">SDC25AG</a>	Assembled Hood Kit, DB25 Metal	3.75	3.52	3.30	3.08	2.85
<a href="#">SDC37AG</a>	Assembled Hood Kit, DB37 Metal	5.00	4.70	4.40	4.10	3.80
<a href="#">SDC50AG</a>	Assembled Hood Kit, DB50 Metal	5.25	4.93	4.62	4.31	3.99

**✓RoHS 4-40 Thumbscrews for SDC Metal and Plastic D-Sub Hood Kits**

Nickel plated steel, knurled, slotted thumbscrews are now available for the entire SDC family of D-Sub hoods. These screws allow the user to secure or remove them either by hand or with a flat blade screwdriver.

<a href="#">04X44S</a>	SDC Thumbscrew, 4-40 Thread	0.35	0.32	0.29	0.27	0.24
------------------------	-----------------------------	------	------	------	------	------

**✓RoHS Replacement Grommets for SDC and SDRA Metal Backshells**

These grommets are the same as supplied with the SDC and SDRA metal backshell kits. Five different sizes are offered per backshell size to best fit cable diameter used.

<a href="#">GROM-9&amp;15</a>	Replacement Grommets, SDC & SDRA 9/15 Metal Backshells	0.65	0.60	0.55	0.49	0.44
<a href="#">GROM-25</a>	Replacement Grommets, SDC & SDRA 25 Metal Backshells	0.65	0.60	0.55	0.49	0.44
<a href="#">GROM-37&amp;50</a>	Replacement Grommets, SDC 37/50 Metal Backshells	0.75	0.69	0.63	0.57	0.51

**✓RoHS Right Angle D-Sub Metal Hood Kits - Low Profile with Thumbscrews**

Right angle hoods offered for applications requiring a 90 degree cable exit. Cast alloy metal construction with a nickel plated finish for the best conductivity. Kit includes five grommets and 4-40 threaded thumbscrews.

<a href="#">SDRA9AG</a>	Right Angle Assembled Hood Kit, DB9 Metal	4.00	3.76	3.52	3.28	3.04
<a href="#">SDRA15AG</a>	Right Angle Assembled Hood Kit, DB15 Metal	4.25	3.99	3.74	3.49	3.23
<a href="#">SDRA25AG</a>	Right Angle Assembled Hood Kit, DB25 Metal	4.50	4.23	3.96	3.69	3.42



**RoHS status information**  
 listed on every product saves you time.  
[L-com.com/RoHS](http://L-com.com/RoHS)

**L-com** Global Connectivity