

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Heavy Duty Cable Cutter - Cuts Copper Multiconductor Cable Clean

This heavy duty cable cutter is ideal for performing clean cuts of multiconductor cable. It offers steel construction and high leverage-extra sharp shears. The HTC60 measures 9.5" in length and can cut copper multiconductor cabling up to 3/4" diameter. Comfortable to use plastic dipped handles.

HTC60	Cable Cutter - to 3/4 inch diameter	19.95	18.35	16.76	15.16	13.57
-----------------------	-------------------------------------	-------	-------	-------	-------	-------

Copper Wire and Light Cable Shears

The HTC1620 is a shear type wire and cable cutter. Straight blades provide clean cuts on soft multiconductor cable up to 3/8" diameter. The tool can also cut copper wire up to 10 AWG. Spring return limits user fatigue by re-opening blades after cut. Includes locking lever to keep blades closed when not in use. Steel construction and plastic coated handles.

HTC1620	Copper and Wire Shears	8.95	8.23	7.52	6.80	6.09
-------------------------	------------------------	------	------	------	------	------

Wire Stripper and Shear - Up to 20 AWG Conductors

The HTC2030 is similar in design to the HTC1620 except it has 6 circular notches for stripping 20-30 AWG wires. The tool also has a small shearing surface for cutting wires. Spring loaded design returns blades to open after use, locking mechanism keeps blades closed when not in use. Steel construction, plastic coated handles.

HTC2030	Wire Stripper and Shear	9.95	9.15	8.36	7.56	6.77
-------------------------	-------------------------	------	------	------	------	------

Rotary Cable Stripper - Cuts Cable Jackets

These tools offer an economical and consistent cable jacket strip every time. Featuring easy to adjust cutting depth, these tools strip both around the cable perimeter and lengthwise. RCS10 strips cable jackets ranging from 0.125" (3.2mm) to 1.0" (25.4mm). MK02 strips cable jackets ranging from 0.18" (4.5mm) to 1.12" (28.5mm). Choose RCS10 for light duty use and MK02 for heavier duty use.

RCS10	Economy Rotary Cable Stripper	14.95	13.75	12.56	11.36	10.17
MK02	Round Cable Stripper	29.95	28.75	27.55	26.36	25.16

RoHS Cable Ties - 4 Sizes in Packs of 100 Pieces

Cable ties come in handy to secure cable assemblies in different applications. Four different sizes are available in packages of 100 pieces each. Color is Black.

CTB-05	6 inch Cable Ties, Pkg/100	6.95	6.53	6.12	5.70	CALL
CTB-07	8 inch Cable Ties, Pkg/100	7.95	7.47	7.00	6.52	CALL
CTB-09	8.5 inch Cable Ties, Pkg/100	8.95	8.41	7.88	7.34	CALL
CTB-12	11.5 inch Cable Ties, Pkg/100	9.95	9.35	8.76	8.16	CALL

Precut Shrink Tubing for Insulating Solder Cups - Packages of 100

This polyolefin shrink tubing is perfectly cut for insulating solder cups on D-Subs. Shrink tubing is 3/32" diameter before shrinkage, the length is 3/8". Packaged in bags of 100 pieces. Color: Black.

SPV332-38	3/32 inch D x 3/8 inch L Shrink Tubing, Pkg/100	4.95	4.65	4.36	4.06	3.76
---------------------------	---	------	------	------	------	------

3M Heat Shrink Tubing Kits

3M's popular kits are versatile assortments of flexible polyolefin heat shrink tubing used in a variety of electronic and electrical applications. Each kit is packaged in a plastic box. These kits allow the engineer, designer or technician a selection of popular sizes and colors for small projects and prototypes. The black kit contains 102 pieces of six inch long tubing in six sizes ranging from 3/16 to 1 inch inside diameter. The color kit contains 133 pieces of six inch long tubing in six sizes ranging from 3/32 to 1/2 inch inside diameter and seven colors. Shrink ratio is 2:1.

SPVFP301-BLK	Heat Shrink Kit, Black Colors	57.95	55.63	53.31	51.00	48.68
SPVFP301-ASST	Heat Shrink Kit, Assorted Colors	57.95	55.63	53.31	51.00	48.68

RoHS 3M Copper Foil Shielding Tape with Conductive Adhesive

Copper foil shielding tape provides an easy to apply, time saving, cost effective way to shield against EMI/RFI radiation. This tape is conductive through the adhesive and offers mechanical, electrical and thermal values to meet shielding effectiveness frequency requirements. Meets UL 510 flame retardancy requirements. 3/8" width is ideal for securing cable shields to backshell grommets. See [page 85](#) for complete backshell offering.

TAP1181-3/8	Copper Foil Shielding Tape, 2.6 MIL x 3/8 inch W x 18 Yards	15.50	14.88	14.26	13.64	13.02
TAP1181-3/4	Copper Foil Shielding Tape, 2.6 MIL x 3/4 inch W x 18 Yards	30.50	29.28	28.06	26.84	25.62

RoHS Cable Labels - Wraparound Style, 3 Sizes to Choose From

We've had multiple requests for wraparound style write on labels to use for cable identification. They are now available, packaged in 30 pieces per package for the occasional user versus 1000 piece packs found elsewhere. Just write or type on the white part of the label, then wrap the clear part over to prevent smudging. There are three sizes to choose from: CL0515 up to 0.275 inch diameter, CL1150 up to 0.275 inch diameter and CL1375 up to 1.000 inch diameter.

CL0515	0.5 in x 1.5 in Wraparound Cable Label, Pkg/30	5.95	5.83	5.71	5.59	5.47
CL1150	1.0 in x 1.5 in Wraparound Cable Label, Pkg/30	7.95	7.79	7.63	7.47	7.31
CL1375	1.0 in x 3.75 in Wraparound Cable Label, Pkg/30	5.95	5.83	5.71	5.59	5.47



Tips
Easy-to-understand tips to help with some of today's popular product applications. L-com.com/Tips