



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Universal Serial Bus 2.0 (USB) Cable Assemblies Allow Transmission Speeds To 480 Mbps

Highest quality USB cables allow for transfer rates up to 480 Mbps. These cables allow for simple Plug and Play connections for devices such as printers, keyboards/mice, digital cameras and other USB peripherals. Twisted pair data lines help reduce crosstalk while heavy AWG power conductors enable maximum power transfer from host to peripheral.

✓RoHS Premium USB Cable - Type A - A Connectors, PVC Jacket, 30 Microinches Gold, 20 AWG Power Leads

CSMUAA-05M	Premium USB Type A - A Cable, 0.5m	7.95	7.31	6.68	6.04	5.41
CSMUAA-1M	Premium USB Type A - A Cable, 1.0m	8.45	7.77	7.10	6.42	5.75
CSMUAA-2M	Premium USB Type A - A Cable, 2.0m	9.45	8.69	7.94	7.18	6.43
CSMUAA-3M	Premium USB Type A - A Cable, 3.0m	10.45	9.61	8.78	7.94	7.11
CSMUAA-4M	Premium USB Type A - A Cable, 4.0m	11.95	10.99	10.04	9.08	8.13
CSMUAA-5M	Premium USB Type A - A Cable, 5.0m	12.45	11.45	10.46	9.46	8.47

✓RoHS Premium USB Cable - Type A - B Connectors, PVC Jacket, 30 Microinches Gold, 20 AWG Power Leads

CSMUAB-05M	Premium USB Type A - B Cable, 0.5m	6.95	6.39	5.84	5.28	4.73
CSMUAB-1M	Premium USB Type A - B Cable, 1.0m	7.45	6.85	6.26	5.66	5.07
CSMUAB-2M	Premium USB Type A - B Cable, 2.0m	8.45	7.77	7.10	6.42	5.75
CSMUAB-3M	Premium USB Type A - B Cable, 3.0m	9.45	8.69	7.94	7.18	6.43
CSMUAB-4M	Premium USB Type A - B Cable, 4.0m	10.45	9.61	8.78	7.94	7.11
CSMUAB-5M	Premium USB Type A - B Cable, 5.0m	11.45	10.53	9.62	8.70	7.79

✓RoHS Premium USB Extension Cable - Type A Connectors, PVC Jacket, 30 Microinches Gold, 20 AWG Power Leads

CSMUAX-1M	Premium USB Type A Male / Female Extension Cable, 1.0m	7.95	7.63	7.31	6.76	5.96
CSMUAX-2M	Premium USB Type A Male / Female Extension Cable, 2.0m	8.95	8.59	8.23	7.61	6.71
CSMUAX-3M	Premium USB Type A Male / Female Extension Cable, 3.0m	9.95	9.55	9.15	8.46	7.46

✓RoHS Deluxe USB Cables - Type A - B Connectors, Revision 2.0 Compliant

L-com's latest USB cable offering, the ECUSB series, provides high performance at competitive prices. These quality constructed cables feature USB 2.0 Compliant 26 AWG power leads and are finished in an attractive medium gray color. Each cable is functionally tested to ensure the highest level of quality and performance. These cables allow for transfer rates up to 480 Mbps and can be used with simple Plug and Play connections for devices such as printers, keyboards/mice, digital cameras and other USB peripherals.

ECUSBAB-05M	Deluxe USB Type A - B Cable, 0.5m	4.35	3.91	3.48	3.04	2.61
ECUSBAB-1M	Deluxe USB Type A - B Cable, 1.0m	4.75	4.28	3.80	3.32	2.85
ECUSBAB-2M	Deluxe USB Type A - B Cable, 2.0m	5.55	5.00	4.44	3.88	3.33
ECUSBAB-3M	Deluxe USB Type A - B Cable, 3.0m	6.35	5.71	5.08	4.44	3.81
ECUSBAB-4M	Deluxe USB Type A - B Cable, 4.0m	7.15	6.44	5.72	5.00	4.29
ECUSBAB-5M	Deluxe USB Type A - B Cable, 5.0m	7.95	7.16	6.36	5.56	4.77

✓RoHS Low Smoke Zero Halogen USB Cable - Type A - B & A - A Connectors, 30 Microinches Gold

Low Smoke Zero Halogen cable reduces the amount of toxic and corrosive gases emitted during combustion. Typically used in poorly ventilated areas, Low Smoke Zero Halogen is becoming very popular where the protection of people and equipment from toxic and corrosive gases is critical.

CSUZAA-05M	LSZH USB Type A - A Cable, 0.5m	12.95	11.91	10.88	9.84	8.81
CSUZAA-1M	LSZH USB Type A - A Cable, 1.0m	14.45	13.29	12.14	10.98	9.83
CSUZAA-2M	LSZH USB Type A - A Cable, 2.0m	17.45	16.05	14.66	13.26	11.87
CSUZAA-3M	LSZH USB Type A - A Cable, 3.0m	20.45	18.81	17.18	15.54	13.91
CSUZAA-5M	LSZH USB Type A - A Cable, 5.0m	26.45	24.33	22.22	20.10	17.99
CSUZAB-05M	LSZH USB Type A - B Cable, 0.5m	12.95	11.91	10.88	9.84	8.81
CSUZAB-1M	LSZH USB Type A - B Cable, 1.0m	14.45	13.29	12.14	10.98	9.83
CSUZAB-2M	LSZH USB Type A - B Cable, 2.0m	17.45	16.05	14.66	13.26	11.87
CSUZAB-3M	LSZH USB Type A - B Cable, 3.0m	20.45	18.81	17.18	15.54	13.91
CSUZAB-5M	LSZH USB Type A - B Cable, 5.0m	26.45	24.33	22.22	20.10	17.99

✓RoHS Premium USB Cable - Type A - Mini B 4 Position, PVC Jacket, 30 Microinches Gold

CSMUAMB4-1M	Premium USB Type A - Mini B 4 Position Cable, 1.0m	8.15	7.34	6.52	5.71	4.89
CSMUAMB4-2M	Premium USB Type A - Mini B 4 Position Cable, 2.0m	9.30	8.37	7.44	6.51	5.58
CSMUAMB4-3M	Premium USB Type A - Mini B 4 Position Cable, 3.0m	10.45	9.40	8.36	7.31	6.27

✓RoHS Premium USB Cable - Type A - Mini B 5 Position, PVC Jacket, 30 Microinches Gold

CSMUAMB5-1M	Premium USB Type A - Mini B 5 Position Cable, 1.0m	8.15	7.34	6.52	5.71	4.89
CSMUAMB5-2M	Premium USB Type A - Mini B 5 Position Cable, 2.0m	9.30	8.37	7.44	6.51	5.58
CSMUAMB5-3M	Premium USB Type A - Mini B 5 Position Cable, 3.0m	10.45	9.40	8.36	7.31	6.27

Premium USB Extension Cable - Mini B 5 Position Male/Female

L-com's CSMUMB5X series cables are designed to connect devices such as GPS units and other USB Mini B 5 position peripherals. All 5 mini B positions are connected to insure proper functionality in every application. We offer these Mini B5 extension cables in off the shelf lengths of 1, 2, and 3 meters. These cables feature foil plus braid shielding to provide maximum protection against EMI/RFI.

CSMUMB5X-1M	Premium USB Mini B 5 Position Cable, Male / Female, 1.0m	8.65	7.79	6.92	6.05	5.19
CSMUMB5X-2M	Premium USB Mini B 5 Position Cable, Male / Female, 2.0m	9.80	8.82	7.84	6.86	5.88
CSMUMB5X-3M	Premium USB Mini B 5 Position Cable, Male / Female, 3.0m	10.95	9.86	8.76	7.66	6.57

"I would like to say that working with L-com has been great. We have had nothing but outstanding customer support and fast shipping. Thank you."
- William Okeson, Electronics Technician, NOAA Ship Delaware II