



Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
✓RoHS ECF504-12AAS	USB Type A Female Shielded Panel Mount Coupler to USB Type A Male Connector, 30 Microinches Gold						
These options feature a bulkhead Type A jack to a molded Type A plug and USB 2.0 compliant cable. Assemblies are fully shielded and can be used in virtually any panel thickness. Recommended 4-40 mounting screws must be purchased separately.							
ECF504-12AAS	USB Type A Coupler, Female Bulkhead / Male, 12 in	Silver	9.95	9.75	9.35	8.76	7.46
ECF504-24AAS	USB Type A Coupler, Female Bulkhead / Male, 24 in	Silver	10.35	10.14	9.73	9.11	7.76
ECF504-36AAS	USB Type A Coupler, Female Bulkhead / Male, 36 in	Silver	10.65	10.44	10.01	9.37	7.99
ECF504-72AAS	USB Type A Coupler, Female Bulkhead / Male, 72 in	Silver	11.55	11.32	10.86	10.16	8.66
ECF504-120AAS	USB Type A Coupler, Female Bulkhead / Male, 120 in	Silver	12.75	12.49	11.98	11.22	9.56
ECF440	Machine Screws, 4-40 x 5/16", Pkg/100		4.35	4.00	3.65	3.31	2.96
✓RoHS ECF504-5M	USB Type A Female Panel Mount Coupler to 5 Meter Un-terminated Pigtail Cable						
This addition to the popular USB panel mount adapter line allows users the flexibility to configure their own assembly. It features a shielded bulkhead Type A Jack with 5 meters of un-terminated USB 2.0 compliant cable. Users can cut the cable to the desired length and hard wire or terminate it with their connector of choice. (See page 96 for compatible USB Type A and B connectors). L-com can custom terminate these cable ends with modest minimum requirements. Recommended 4-40 mounting screws must be purchased separately.							
ECF504-5M	USB Type A Female Panel Mount Coupler / 5.0m Cable		11.95	11.71	11.23	10.52	8.96
ECF440	Machine Screws, 4-40 x 5/16", Pkg/100		4.35	4.00	3.65	3.31	2.96
✓RoHS ECJ504-UA	USB Type A and B Panel Couplers with 10" Wire Leads, 30 Microinches Gold						
Similar to our ECF504 USB coupler except with wire leads in the rear to connect to equipment. Choose from USB Type A or B jacks in Black or Ivory. Wires are 20 AWG (2 power) and 24 AWG (2 signal) stranded wires with an additional drain to shield. Recommended 4-40 mounting screws must be purchased separately.							
ECJ504-UA	USB Type A Jack, 10" Leads	Ivory	5.25	5.14	4.93	4.62	3.94
ECJ504-UB	USB Type B Jack, 10" Leads	Ivory	5.25	5.14	4.93	4.62	3.94
ECJ504B-UA	USB Type A Jack, 10" Leads	Black	5.25	5.14	4.93	4.62	3.94
ECJ504B-UB	USB Type B Jack, 10" Leads	Black	5.25	5.14	4.93	4.62	3.94
ECF440	Machine Screws, 4-40 x 5/16", Pkg/100		4.35	4.00	3.65	3.31	2.96
✓RoHS UPMMA-M	USB Type A Female Panel Mount to Type A Male Cable Assembly						
These USB 2.0 panel mount cables are perfect for use inside a box or enclosure. The USB Type A female side is flange-style panel mountable with an alternative, smaller body compared to the popular ECF504 series. This makes it a nice fit in applications with limited space. The molded panel mountable USB construction is rugged and robust, using 20 AWG power conductors and a 28 AWG twisted pair all under a double shield for maximum EMI resistance. 2 pieces of 4-40 x 3/8" Phillips pan head mounting screws included. Quantity and custom length pricing available, just give us a call!							
UPMAA-05M	USB Cable Assembly, Type A Female Panel Mount / Type A Male, 0.5m	Lt. Gray	8.45	7.77	7.10	6.42	5.75
UPMAA-1M	USB Cable Assembly, Type A Female Panel Mount / Type A Male, 1.0m	Lt. Gray	8.95	8.23	7.52	6.80	6.09
UPMAA-2M	USB Cable Assembly, Type A Female Panel Mount / Type A Male, 2.0m	Lt. Gray	9.95	9.15	8.36	7.56	6.77
UPMAA-3M	USB Cable Assembly, Type A Female Panel Mount / Type A Male, 3.0m	Lt. Gray	10.95	10.07	9.20	8.32	7.45
UPMAA-5M	USB Cable Assembly, Type A Female Panel Mount / Type A Male, 5.0m	Lt. Gray	12.95	11.91	10.88	9.84	8.81
✓RoHS UPMMA-5M	USB Type A Female Panel Mount to 5 Pin Female 0.100"/2.54mm Header Connector						
Designed to make "board-to-box" USB connections a cinch, this light, flexible USB cable uses a pre-installed 5 pin female housing to a molded flange-mount USB type A female. Look no further for your USB panel mount solution! The cable is double shielded for maximum EMI resistance and the power conductors are 26 AWG to make the overall cable more flexible. Quantity and custom length pricing available, just give us a call!							
UPMA5-03M	USB Cable Assembly, Type A Female Panel Mount / 5 Pin Female, 0.3m	Lt. Gray	7.19	6.61	6.04	5.46	4.89
UPMA5-1M	USB Cable Assembly, Type A Female Panel Mount / 5 Pin Female, 1.0m	Lt. Gray	7.75	7.13	6.51	5.89	5.27
UPMA5-2M	USB Cable Assembly, Type A Female Panel Mount / 5 Pin Female, 2.0m	Lt. Gray	8.55	7.87	7.18	6.50	5.81
✓RoHS CSMUAXMT-	Mountable USB Extension Cable - Type A Connectors, 30 Microinches Gold						
Tired of trying to connect your USB cable to the hard to access port on the back of your PC? Try this convenient cable and make this problem go away! Featuring a USB Type A plug for the PC connection and a unique USB Type A jack, the user can mount this jack to any surface with either screws or double sided foam tape (both are provided). Fully shielded and USB 2.0 compliant, this cable contains two 20 AWG power conductors plus one 28 AWG twisted pair for the data lines and rugged molded backshells. Cable length is 2 meters (6.6 feet). Color is Light Gray.							
CSMUAXMT-	Premium USB Type A Male / Female Mounting Extension Cable, 2.0m	Lt. Gray	10.50	9.66	8.82	7.98	7.14




Tip Advantage of using the USB mountable extension cable assembly

Connecting a cable to the hard to access USB port on your PC can be difficult.



Simply connect the mountable extension cable once to the USB port on the back of your computer.



This cable can be mounted to your PC monitor or any work surface. Choose your preferred mounting option using either the double sided adhesive tape or screws provided. Your USB port is now easy to access.

Suggested Uses:

- Digital Cameras
- External Hard Drives
- MP3 Players
- Test Environments

✓RoHS Variable Length USB Coil Cable - Mini B 5 Position Male/Female

This innovative USB coil cable from L-com features a retracted length 0.5 meters and an expanded length of two meters and can be used with GPS systems as well as cameras and other peripherals using the USB Mini B5 interface. All 5 mini B positions are connected to insure proper functionality in every application. The tough, durable polyurethane jacket enhances recoil memory and 30 microinch gold plated contacts provide reliable connections with repeated mating cycles. Order online today!

COILMB5EXT-2M	USB Coil Cable - Mini B 5 Position Male / Female, 0.5m to 2.0m	Black	11.50	10.58	9.66	8.74	7.82
---------------	--	-------	-------	-------	------	------	------

"I just wanted to say "thank you" for doing what you do. Your products are great, your customer service is excellent, your website is easy to navigate and use, and best of all your prices are very competitive. You guys have earned a lifetime customer here." - Phil Stark, Network Engineer, The Matrix Group