




CSUSB




CNUSB-A

CNUSB-B



HOODUSB-

HOODUSB-



USBFAFT



CAPUSB-A

CAPUSB-B



CAPUSB-MB5



ZN-ZUN2200



ZN-ZUC2401



ZN-ZUH2215V

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
USB Revision 2.0 Compliant Bulk Cable	This cable will support the 480 Mbps transmission rate of a USB 2.0 network and is also backward compatible with older, slower USB networks. USB bulk cable features two 20 AWG power conductors plus one 28 AWG twisted pair for the data lines. A flexible PVC jacket covers the braid, foil and drain wire shield. Choose from 100, 500 or 1000 foot spools. Jacket color is Light Gray.						
CSUSB-100	USB Revision 2.0 Compliant Bulk Cable, 100 ft Spool	Lt. Gray	49.00	46.06	43.12	40.18	CALL
CSUSB-500	USB Revision 2.0 Compliant Bulk Cable, 500 ft Spool	Lt. Gray	225.00	211.50	198.00	184.50	CALL
CSUSB-1000	USB Revision 2.0 Compliant Bulk Cable, 1000 ft Spool	Lt. Gray	395.00	371.30	347.60	323.90	CALL

USB Connectors and Hoods, Type A and B

USB connectors and hoods are now available for custom lengths and applications. The USB connector system is becoming the connector of choice for many applications due to its low material and labor costs. Connectors feature gold plated solder contacts, nickel-plated steel shells and a UL94V-0 rated housing. Hoods are Light Gray ABS resin and are also UL94V-0 rated.

CNUSB-A	USB Type A Connector		1.39	1.36	1.31	1.22	1.04
CNUSB-B	USB Type B Connector		1.39	1.36	1.31	1.22	1.04
HOODUSB-	USB Type A Hood	Lt. Gray	0.58	0.57	0.55	0.51	0.43
HOODUSB-	USB Type B Hood	Lt. Gray	0.58	0.57	0.55	0.51	0.43

USB A Style Female Connector for Field Termination

The USBFAFT field termination female connector provides an easy and convenient way to perform field termination for USB applications. Separate connection points are provided for all 4 positions of the connector plus the ground. Terminal block design with set screws provides reliable electrical connections utilizing no special tools. The terminal block area is clearly marked making proper termination virtually foolproof. Panel mountable using 4-40 screws provided.

USBFAFT	USB Field Termination Connector, Type A Female		6.25	5.88	5.50	5.13	4.75
-------------------------	--	--	------	------	------	------	------

USB Type A, B and Mini B5 Connector Covers - Protect Unused Ports, Pkg/10

These covers are perfect for protecting unused female ports in our panel mount couplers or any expensive equipment from physical damage, dirt and dust. Made from soft ABS, these covers attach easily and stay in place with a snug friction fit. Color: Black.

CAPUSB-A	USB Protective Cover for Type A Jacks, Pkg/10	Black	6.50	5.98	5.46	4.94	4.42
CAPUSB-B	USB Protective Cover for Type B Jacks, Pkg/10	Black	6.50	5.98	5.46	4.94	4.42
CAPUSB-MB5	USB Protective Cover for Type Mini B5 Jacks, Pkg/10	Black	6.50	5.98	5.46	4.94	4.42

Zonet 2 Port USB 2.0 32-Bit CardBus Type-II PC Card

The ZN-ZUN2200 quickly adds two high-speed USB 2.0 ports to your laptop. This PC card fits any CardBus Type-II slot and supports Windows 98SE/ME/2000/XP operating systems. Plug and play installation insures easy installation. Includes a 1-year manufacturer's warranty.

ZN-ZUN2200	Zonet 2 Port USB PC Card		30.00	29.40	28.80	28.20	27.60
----------------------------	--------------------------	--	-------	-------	-------	-------	-------

Zonet 4 Port USB 2.0/2 Port Firewire PCI Combo Card

The ZN-ZUC2401 is a flexible and versatile PCI card featuring three USB 2.0 and 2 IEEE1394 Firewire ports to your PC. This easy to install, plug and play PCI card supports USB data rates of 1.5/12/480 Mbps as well as Firewire data speeds of 100/200/400 Mbps. Windows 98SE/ME/2000/XP/Vista operating systems are supported. Includes a 1-year manufacturer's warranty.

ZN-ZUC2401	Zonet 4 Port USB PCI Combo Card		39.00	38.22	37.44	36.66	35.88
----------------------------	---------------------------------	--	-------	-------	-------	-------	-------

Zonet 4 Port USB 2.0 PCI Card

The ZN-ZUH2215V features four High-speed USB 2.0 ports along with easy plug and play installation. By utilizing the ZN-ZUH2215V, you can add four USB 2.0 ports to your existing PC. This versatile PCI card supports data transfer speeds of 1.5/12/480 Mbps. Works with Windows 98SE/ME/2000/XP. Includes a 1-year manufacturer's warranty.

ZN-ZUH2215V	Zonet 4 Port USB PCI Card		19.00	18.62	18.24	17.86	17.48
-----------------------------	---------------------------	--	-------	-------	-------	-------	-------



Tip *USB supports three different speeds:*

- **Low-speed** devices operate at 1.5 Mbps (megabits per second). Examples include keyboards, mice and serial interfaces such as RS232. USB version 1.0 and 1.1 compliant devices provide enough bandwidth for these applications.
- **Full-speed** devices operate at 12 Mbps. Examples include web-cams and printers. Typically, USB versions 1.0 and 1.1 will provide enough bandwidth to meet these requirements.
- **High-speed** devices operate at 480 Mbps. These devices include external CD-ROM, DVD drives and USB to Ethernet applications. USB version 2.0 is the preferred version for these types of applications.

USB 2.0, or high speed USB, is backward compatible with USB versions 1.0 and 1.1. USB 2.0 supports low-bandwidth devices such as keyboards and mice, as well as high-bandwidth devices including webcams, scanners, printers and storage devices.

