



Item #	Code	Description	Spaces	Height	Shipping Weight	1-9	10-24	25-99	100-249
--------	------	-------------	--------	--------	-----------------	-----	-------	-------	---------

RoHS 19" Steel Lockboxes - 9" Depth Allows Rack Mountable Security

Safely secure gear in the LBX series of lockboxes. 3 and 4 rack space models are available, both are 9" deep. Black powder coat finish.

LBX-3	A	19" Rack Mountable Lockbox	3	5.25 in	11 lbs	76.02	72.22	67.65	65.37
LBX-4	A	19" Rack Mountable Lockbox	4	7.00 in	12 lbs	82.63	78.50	73.54	71.06

RoHS 19" Steel Utility Drawer in 2, 3 and 4 Rack Space Heights

These steel utility drawers are available in two, three and four rack space heights for storing equipment and supplies. Full extension ball bearing slides smoothly extending to a full 14" (inside dimensions 15 7/8" x 14 1/2"). Knockouts in rear allow cable pass through. Black powder coat finish.

UD-2	B	19" Rack Mountable Utility Drawer	2	3.50 in	16 lbs	99.97	94.97	88.97	85.97
UD-3	B	19" Rack Mountable Utility Drawer	3	5.25 in	19 lbs	106.44	101.11	94.73	91.53
UD-4	B	19" Rack Mountable Utility Drawer	4	7.00 in	21 lbs	122.63	116.50	109.14	105.46

RoHS 3 1/2" and 5 1/4" High (2 and 3 Rack Spaces) Heavy Duty Shelves for 19" Racks

Two heavy duty shelves are available for 19" rack panels. Cantilever shelf is 17" deep and occupies three rack spaces vertically. The center weight shelf is 18" long in total and occupies two rack spaces vertically. Both shelves have vented bottoms. Color: Matte Black.

U317	C	19" Rack Mountable Heavy Duty Cantilever Shelf, 17" Dp.	3	5.25 in	10 lbs	58.68	55.74	52.22	50.46
U2MS	D	19" Rack Mountable Heavy Duty Center Weight Shelf, 18" Dp.	2	3.50 in	9 lbs	62.47	59.34	55.60	53.72

RoHS 19" Rackmount Slide-Away Computer Keyboard System

The rackmount computer keyboard system occupies only 1 3/4" (1 space) and features a high quality keyboard with built in trackball. A built in cable support arm provides secure cable management.

RM-KB-LCD17	E	19" Rackmount Slide-Away 17" LCD Monitor, Keyboard and Touchpad	1	1.75 in	35 lbs	1845.00	1752.75	1642.05	1586.70
RM-KB	F	19" Rackmount Computer Keyboard with Trackball	1	1.75 in	16 lbs	395.45	375.68	351.95	340.09

RoHS 19" Rackmount Sliding Shelves

The rackmount sliding shelves extend out giving easy access to equipment. A telescopic rear support offers flexibility in rack mounting depths. Each shelf requires a minimum rack depth of 14.75".

SSL	G	19" Sliding Shelf w/14" x 16.75" Work Surface, 35 lb Capacity	1	1.75 in	9 lbs	77.74	73.85	69.19	66.86
SS	H	19" Sliding Shelf w/14.75" x 17.5" Work Surface, 50 lb Capacity	1+	2.40 in	15 lbs	115.10	109.34	102.44	98.98

RoHS 19" Rack Filler Panels

A variety of 19" rack filler panels allow installers to give a custom look to their rack installation while allowing proper thermal venting.

PR175BLK	I	1.75" Blank Filler Panel, Solid Steel	1	1.75 in	1 lb	20.85	19.18	17.51	15.85
PR35BLK	I	3.50" Blank Filler Panel, Solid Steel	2	3.50 in	2 lbs	27.45	25.25	23.06	20.86
PR175-EVTBLK	J	1.75" Blank Filler Panel, Vertical Vented Steel	1	1.75 in	1 lb	8.77	8.34	7.81	7.55
PR35-EVTBLK	J	3.50" Blank Filler Panel, Vertical Vented Steel	2	3.50 in	1 lb	11.47	10.89	10.21	9.86
PR175-VTPBLK	K	1.75" Blank Filler Panel, Horizontal Vented Steel	1	1.75 in	1 lb	20.53	19.51	18.27	17.66
PR35-VTPBLK	K	3.50" Blank Filler Panel, Horizontal Vented Steel	2	3.50 in	1 lb	22.44	21.31	19.97	19.29
FILTER	L	5.25" x 19" Rack Filter	3	5.25 in	1 lb	29.15	27.69	25.94	25.06
OTFP-2	L	5.25" x 19" Panel with Dual 4.5" Fans	3	5.25 in	5 lbs	105.63	100.35	94.01	90.84

"L-com's e-mails pointing out answers to questions and getting people to start using your website as a knowledge based resource is an excellent marketing idea, but also an excellent resource. Educating our colleagues is a vital part of keeping our technological superiority over the competition whether it is business or national defense." - Joe Gannatal, Supervisory Electronics Engineer, U.S. Navy