

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Domestic and International Power Cords - UL/CSA or European Approved

L-com now stocks several popular external power cords for domestic, international and medical applications. All assemblies are fully molded and meet the required safety specifications.

✓RoHS Domestic Power Cords - UL/CSA Approved

Connector options include N5/15, C7, C13, N1/15 and a pigtail end. Heavy duty cable is 18 AWG, color is Black.

PCM1000	Power Cord SPT2-18 AWG, N1/15P-EN60320C7, UL/CSA, 6'7"	3.95	3.79	3.63	3.48	3.32
PCM1010	Power Cord SVT3-18 AWG, N5/15-Pigtail, UL/CSA, 6'7"	4.95	4.75	4.55	4.36	4.16
PCM1012	Power Cord SVT3-18 AWG, N5/15-EN60320C13, UL/CSA, 7'6"	5.45	5.23	5.01	4.80	4.58
PCM1014	Power Cord SJT3-18 AWG, N5/15-EN60320C13, UL/CSA, 9'10"	5.95	5.71	5.47	5.24	5.00

Colored Domestic Power Cords - UL/CSA Approved

PCM1012-B	Power Cord SVT3-18 AWG, N5/15-EN60320C13, UL/CSA, 7'6", Blue	5.95	5.71	5.47	5.24	5.00
PCM1012-C	Power Cord SVT3-18 AWG, N5/15-EN60320C13, UL/CSA, 6", Caramel Brown	1.49	CALL	CALL	CALL	CALL
PCM1012-G	Power Cord SVT3-18 AWG, N5/15-EN60320C13, UL/CSA, 7'6", Green	5.95	5.71	5.47	5.24	5.00
PCM1012-R	Power Cord SVT3-18 AWG, N5/15-EN60320C13, UL/CSA, 7'6", Red	5.95	5.71	5.47	5.24	5.00
PCM1012-Y	Power Cord SVT3-18 AWG, N5/15-EN60320C13, UL/CSA, 7'6", Yellow	5.95	5.71	5.47	5.24	5.00

✓RoHS Hospital Grade Power Cords - UL/CSA Approved

Connectors are Hospital Grade N5/15 to C13. 18 AWG cable is Gray, connector mold options are Gray and Clear.

PCM1050	Power Cord Gray Mold, SJT3-18 AWG, N5/15-EN60320C13, UL/CSA, 10'	9.45	9.07	8.69	8.32	7.94
PCM1052	Power Cord Clear Mold, SJT3-18 AWG, N5/15-EN60320C13, UL/CSA, 10'	9.45	9.07	8.69	8.32	7.94

✓RoHS International Power Cords - Meets VDE and Several Other Approvals

Connector options are CEE7/7 to C13 and EN50075 to C7, color is Black.

PCM1020	Power Cord H05VVF3Gx1.00mm, CEE7/7- EN60320C13, VDE, 8'2"	7.95	7.63	7.31	7.00	6.68
PCM1030	Power Cord H03VWH2F2X0.75mm, EN50075-EN60320C7, VDE, 6'	6.95	6.67	6.39	6.12	5.84
SP23917	Power Cord Danish 107 to EN60 320 (C13) 2.5 meters	2.49	CALL	CALL	CALL	CALL
SP23913	Power Cord Chinese EN60320 C13 2.5 meters	1.79	CALL	CALL	CALL	CALL

✓RoHS Universally Approved Jumper Cords - Domestic and European Approved, UL/CSA, VDE

Connectors are C13 to C14, lengths are 3'3", 6'7" and 9'10". Heavy duty cable is 18 AWG, color is Black.

PCM1040	Power Cord SJT3-18 AWG, EN60320C13/C14, UL/CSA VDE, 3'3"	4.95	4.75	4.55	4.36	4.16
PCM1042	Power Cord SJT3-18 AWG, EN60320C13/C14, UL/CSA VDE, 6'7"	5.95	5.71	5.47	5.24	5.00
PCM1044	Power Cord SJT3-18 AWG, EN60320C13/C14, UL/CSA VDE, 9'10"	6.95	6.67	6.39	6.12	5.84

Switching Power Supplies, Power Cords, PoE Power Supplies and Lighter Power Adapters

We offer a broad range of switching power supplies which support 110/220 VAC operation. Models in this series include 9 VDC, 12 VDC, 15 VDC and 48 VDC options. Additionally, PoE power supplies are available which provide data and power over a single CAT5 cable to end devices which are compliant with IEEE standard PoE pinout (Pins 4&5 Power +/Pins 7&8 Power -).

The HyperLink brand PS4820-POE is a power supply with integral DC injector. It provides DC power for one PoE-equipped device by "injecting" DC power through the CAT5 Ethernet cable. It is compatible with AP's and other equipment supporting the IEEE standard PoE pinout (Pins 4&5 Power +/Pins 7&8 Power -). This unit can also be used with Cisco PoE equipment using the optional PoE conversion cable.

Since the PS4820-POE is completely self-contained, a separate power supply and injector is not required. The PS4820-POE features an impact resistant polycarbonate enclosure and includes a 3-prong detachable power cord.

- 9V, 12V, 15V, 48 VDC models available
- Use with PoE injectors/taps, wireless radios, RF amplifiers and more
- 20 W and 60 W PoE power supplies

✓RoHS Switching Power Supplies


PS909-21R	9 VDC @ 1A (9W), 2.1mm DC Plug	9.99	9.59	9.19	8.49	7.49
PS1212-21R	12 VDC @ 1A (12W), 2.1mm Right Angle DC Plug	21.99	21.11	20.23	18.69	16.49
PS1224-21R	12 VDC @ 2A (24W), 2.1mm Right Angle DC Plug	24.99	23.99	22.99	21.24	18.74
PS1240-21R	12 VDC @ 3.33A (40W), 2.1mm Right Angle DC Plug	64.99	62.39	59.79	55.24	48.74
PS1566	15 VDC @ 4.4A (66W), 2.1mm DC Plug	89.99	86.39	82.79	76.49	67.49
PS4820-POE	48 VDC @ 0.83A (20W), Dual RJ45 PoE, Includes Power Cord	39.99	38.39	36.79	33.99	29.99
PS4870-25R	48 VDC @ 1.5A (70W), 2.5mm Right Angle DC Plug	59.00	56.64	54.28	50.15	44.25
PS4848-25R	48 VDC @ 1A (48W) 2.5mm Right Angle DC Plug	21.00	20.16	19.32	17.85	15.75
PS4860-POE	48 VDC @ 1.25A (60W), Dual RJ45 PoE, Requires PSCORD3	74.99	71.99	68.99	63.74	56.24

12 VDC to 48 VDC Converter/Regulator

PS-LIGHTER-06	Cigarette Plug to 2.1mm Right Angle DC Plug, 3A Fuse, 6ft	9.99	9.59	9.19	8.49	7.49
-------------------------------	---	------	------	------	------	------

✓RoHS Accessories

PSX-EU1	US Flat or Euro Round to Euro 4.8mm Round A/C Adapter	3.99	3.59	3.19	2.79	2.39
PSX-EU2	EU 4/4.8mm Round to US NEMA 6-15R Flat A/C Adapter	3.99	3.59	3.19	2.79	2.39
PSCORD2	2 Conductor Plug, USA/AC Power Cord, 1ft	3.99	3.59	3.19	2.79	2.39
PSCORD3	3 Conductor Plug, USA/AC Power Cord, 1ft	2.99	2.75	2.51	2.27	2.03
CA-POE-02	CAT5 PoE Conversion Cable for Cisco APs, 2ft	14.99	13.49	11.99	10.49	8.99



Certifications

A complete company documentation package is available for download. L-com.com/Profile