

Item #	Description	Maximum Segment Length	List Price
<b>Metrobility Radiance Series Converter Chassis - 1, 2 and 17 Slot Options</b>			
<a href="#">LCR5000-17HS</a>	17 Slot Radiance 19" Rack Mountable Chassis		479.00
<a href="#">LCACPS-17HS</a>	AC Power Supply for the LCR5000 Chassis		109.00
<a href="#">LCDPCS-17HS</a>	DC Power Supply for the LCR5000 Chassis		469.00
<a href="#">LCR1000-AAF</a>	2 Slot Chassis with 2 Front Facing AC Power Supplies		539.00
<a href="#">LCR200-AC</a>	1 Slot Chassis with Single AC Power Supply		249.00
<a href="#">LCR200-DC</a>	1 Slot Chassis with Single DC Power Supply		259.00

**Metrobility Radiance SNMP Management Module**

<a href="#">LCR502-M</a>	SNMP Management Module for Radiance R5000 Chassis		489.00
--------------------------	---	--	--------

**Gigabit Ethernet (1Gbps) "Twister" Modules for Radiance Series Chassis**

<a href="#">LCR152-1A</a>	1000Base-TX, RJ45 to 1000Base-SX, Multimode SC	100m/220m	489.00
<a href="#">LCR152-1D</a>	1000Base-TX, RJ45 to 1000Base-LX, Single mode SC	100m/10km	689.00
<a href="#">LCR152-1F</a>	1000Base-TX, RJ45 to 1000Base-LX, Single mode SC	100m/25km	1519.00
<a href="#">LCR152-AD</a>	1000Base-SX, Multimode SC to 1000Base-LX, Single mode SC	220m/10km	829.00

**100 Mbps Fast Ethernet "Twister" Modules for Radiance Series Chassis**

<a href="#">LCR231-13</a>	100Base-TX, RJ45 to 100Base-FX, Multimode SC	100m/2km	489.00
<a href="#">LCR231-15</a>	100Base-TX, RJ45 to 100Base-FX, Multimode ST	100m/2km	449.00
<a href="#">LCR231-16</a>	100Base-TX, RJ45 to 100Base-FX, Single mode ST	100m/15km	689.00
<a href="#">LCR231-17</a>	100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/40km	829.00
<a href="#">LCR231-1J</a>	100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/100km	2199.00

**10/100 Mbps Ethernet Intelligent AutoTwister Modules for Radiance Series Chassis**

<a href="#">LCR643-13</a>	10/100Base-TX, RJ45 to 100Base-FX, Multimode SC	100m/2km	209.00
<a href="#">LCR643-15</a>	10/100Base-TX, RJ45 to 100Base-FX, Multimode ST	100m/2km	259.00
<a href="#">LCR643-1K</a>	10/100Base-TX, RJ45 to 100Base-FX, Multimode LC	100m/2km	309.00
<a href="#">LCR643-14</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/15km	365.00
<a href="#">LCR643-17</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/40km	399.00
<a href="#">LCR643-1J</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/100km	1379.00
<a href="#">LCR643-1M</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode LC	100m/15km	419.00

**Gigabit Ethernet (1Gbps) Twister Stand-alone Media Converters**

<a href="#">LC2152-1A</a>	1000Base-TX, RJ45 to 1000Base-SX, Multimode SC	100m/220m	759.00
<a href="#">LC2152-1D</a>	1000Base-TX, RJ45 to 1000Base-LX, Single mode SC	100m/10km	1179.00
<a href="#">LC2152-1F</a>	1000Base-TX, RJ45 to 1000Base-LX, Single mode SC	100m/25km	1779.00
<a href="#">LC2152-AD</a>	1000Base-SX, Multimode SC to 1000Base-LX, Single mode SC	220m/10km	1319.00

**10/100 Mbps Fast Ethernet Twister Stand-alone Media Converters**

<a href="#">LC2643-13</a>	10/100Base-TX, RJ45 to 100Base-FX, Multimode SC	100m/2km	249.00
<a href="#">LC2643-15</a>	10/100Base-TX, RJ45 to 100Base-FX, Multimode ST	100m/2km	279.00
<a href="#">LC2643-1K</a>	10/100Base-TX, RJ45 to 100Base-FX, Multimode LC	100m/2km	309.00
<a href="#">LC2643-14</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/15km	379.00
<a href="#">LC2643-17</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/40km	419.00
<a href="#">LC2643-1J</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode SC	100m/100km	1419.00
<a href="#">LC2643-1M</a>	10/100Base-TX, RJ45 to 100Base-FX, Single mode LC	100m/15km	419.00

**Unicom 10Base-FL/10Base-T (Fiber/UTP) Converters - Dual ST and RJ45 Connections**

These media converters conform with the IEEE 802.3 Ethernet fiber optic standard (10Base-FL). Dual Fiber ST connectors allow connection to 62.5/125 duplex multimode or single mode cabling and electro optic circuitry transforms the signal to a 10Base-T RJ45 port. Multimode fiber runs can extend up to 2km and single mode runs to 20km. Two position switch allows 10Base-T connection to a hub or a workstation and seven LEDs indicate network status at all times. Externally powered with 9V DC transformer included.

<a href="#">UTP20108</a>	Miniature 10Base-FL/10Base-T Multimode Converter	169.00
<a href="#">UTP20108-SM</a>	Miniature 10Base-FL/10Base-T Single mode Converter	400.00

**Unicom 10Base-T/AUI Transceiver - RJ45 and DB15 Male Connections**

Use this transceiver to connect your existing thick Ethernet interface card to a 10Base-T UTP network. Converts signals from standard Ethernet transceiver cable to a suitable format for transmission over Unshielded Twisted Pair wires to a hub of your choice. Our mini 10Base-T transceiver does not require any external power. Includes a set switch for enabling or disabling the SQE function for applications that require the SQE test. The POWER/ TX, LINK/RCV and COLLISION/JABBER LED lights simplify troubleshooting and network maintenance.

<a href="#">UTP20028T</a>	Miniature 10Base-T/AUI Transceiver	29.00
---------------------------	------------------------------------	-------

**Unicom 10Base-2/10Base-T Media Converter - RJ45 and BNC Connections**

This 10Base-2/T converter is designed to connect your existing Thin Ethernet interface card or Thin Ethernet Network to a 10Base-T UTP network. The unit simply converts signals from Thin Ethernet to a suitable form for transmission over Unshielded Twisted Pair (UTP). It has a three position terminator switch (open, 25 Ohm, 50 Ohm) for varying applications. The POWER, LINK, TPPLR, TPRCV, TPCOL, CXCOL, CXRCV LED lights simplify troubleshooting and network maintenance. Supplied with 9V DC power adapter.

<a href="#">UTP20038T</a>	Miniature 10Base-2/T Converter	69.00
---------------------------	--------------------------------	-------



"Your eNewsletter is always very topical. I like its brevity with a link to more info if needed. It's always informative and to the point. Keep up the good work. Thank you." - James K.