

Item #	Style	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS 2.4 GHz Wide Angle Patch Antennas							
These compact 2.4 GHz WiFi antennas provide 5 dBi Gain with broad horizontal beam width of 135 degrees. They are ideally suited for applications requiring coverage of a wide area such as an office, public hotspot, Industrial or warehouse use. These antennas are lightweight and feature an aesthetic UV-stable, white ABS UL Flame Rated radome and can also be painted to match the room or building structure. The HG2405P-135 can be installed for horizontal or vertical polarization.							
HG2405P-135-NF	E*	5 dBi, Wide Angle, 12in (30.5cm) N Female Connector	32.99	31.01	29.03	27.05	25.07
HG2405P-135-NM	E*	5 dBi, Wide Angle, 4ft (1.2m). N Male Connector	32.99	31.01	29.03	27.05	25.07
HG2405P-135-RSP	E*	5 dBi, Wide Angle, 4ft (1.2m). RP-SMA Plug Connector	32.99	31.01	29.03	27.05	25.07
HG2405P-135-RTP	E*	5 dBi, Wide Angle, 4ft (1.2m). RP-TNC Plug Connector	32.99	31.01	29.03	27.05	25.07
HG2405SD-135-NF	E	5 dBi, Wide Angle Spatial Diversity, 12in (30.5cm) Dual N Female Connectors	37.99	34.95	31.91	28.87	25.83
HG2405SD-135-NM	E	5 dBi, Wide Angle Spatial Diversity, 4ft (1.2m). Dual N Male Connectors	39.99	36.79	33.59	30.39	27.19
HG2405SD-135-RSP	E	5 dBi, Wide Angle Spatial Diversity, 4ft (1.2m). Dual RP-SMA Plug Connectors	39.99	36.79	33.59	30.39	27.19
HG2405SD-135-RTP	E	5 dBi, Wide Angle Spatial Diversity, 4ft (1.2m). Dual RP-TNC Plug Connectors	39.99	36.79	33.59	30.39	27.19

*Similar to this antenna, but with one antenna lead.

✓RoHS 2.4/5.8 GHz Wide Angle Patch Antennas

These compact 2.4/5.8 GHz WiFi antennas provide Dual Frequency diversity to improve connectivity and data throughput. They provide wide angle pattern to give the provider excellent area coverage from one antenna site.

HG2458-5P-135-NF	E	5 dBi, Wide Angle, 12in (30.5cm) N Female Connector	39.99	36.79	33.59	30.39	27.19
HG2458-5P-135-NM	E	5 dBi, Wide Angle, 12in (30.5cm) N Female Connector	41.99	38.63	35.27	31.91	28.55
HG2458-5P-135-RSP	E	5 dBi, Wide Angle, 12in (30.5cm) N Female Connector	41.99	38.63	35.27	31.91	28.55
HG2458-5P-135-RTP	E	5 dBi, Wide Angle, 12in (30.5cm) N Female Connector	41.99	38.63	35.27	31.91	28.55

✓RoHS 2.4/5.8 GHz Patch Antenna

HG2458-09P	A	9 dBi, Flat Patch, with Integral N Female Connector	69.99	64.39	58.79	53.19	47.59
HG2458-20P	A	20 dBi, 2.4 GHz/5.1-5.8 GHz Flat Patch, with Integral N Female Connector	124.99	119.99	114.99	109.99	104.99
HG2458-14DP-3NF	A	14 dBi, 2.4 GHz/5.8 GHz Dual Polarized Panel with N Female Connector	124.99	112.49	99.99	87.49	74.99

✓RoHS 2.6 GHz Patch Antenna

HG2614P-NF	A	14 dBi, 8in (20.3cm) Square, 12in (30.5cm) Pigtail with N Female Connector	44.99	40.49	35.99	31.49	26.99
------------	---	--	-------	-------	-------	-------	-------



Tip Custom Manufacturing

L-com is unique among most WiFi antenna vendors by also being an antenna manufacturer. Being a manufacturer allows us to provide custom variations of all the antennas we manufacture in house or resell. A typical custom request may be to change the length of an antenna lead or pigtail to accommodate a specific installation of the antenna. Another may be a change to the connector or connectors required for a specific radio connection. In most cases we can ship out a large custom order in less than a week. Small custom orders are usually shipped on the same day they are received. L-com offers a broad range of antenna types covering 800 – 6000 MHz. Learn more at L-com.com.

3.5 GHz, 4.9 GHz, 5.1 GHz, 5.3 GHz, 5.4 GHz and 4.9/5.8 GHz Patch Antennas

L-com's extensive line of patch antennas that cover frequencies from 3.5 to 5.8 GHz are ideal for applications such as WiMax and public safety. Several of the patch antennas are broadband/multi-band antennas that eliminate the need to purchase different antennas for each frequency being used. This simplifies installations since the same antenna can be used for a wide array of wireless applications.

✓RoHS 3.5 GHz Patch Antennas

HG3509P-NF	A	8 dBi, 4in (10.2cm) Square, 12in (30.5cm) Pigtail with N Female Connector	39.99	35.99	31.99	27.99	23.99
HG3514P-NF	A	14 dBi, 8in (20.3cm) Square, 12in (30.5cm) Pigtail with N Female Connector	49.99	44.99	39.99	34.99	29.99

✓RoHS 4.9 GHz Patch Antennas

HG4953P	A	8 dBi, 4in (10.2cm) Square, Broadband, Integral SMA Male Connector	49.99	44.99	39.99	34.99	29.99
HG4911P	A	11 dBi, 4in (10.2cm) Square, Integral SMA Female Connector	49.99	44.99	39.99	34.99	29.99

✓RoHS 5.3 GHz Patch Antenna

HG5311P	A	11 dBi, 4in (10.2cm) Square, Integral SMA Female Connector	49.99	44.99	39.99	34.99	29.99
---------	---	--	-------	-------	-------	-------	-------

✓RoHS 5.4 GHz Patch Antennas

HG5411P	A	11 dBi, 4in (10.2cm) Square, Integral SMA Female Connector	49.99	47.99	45.99	42.49	37.49
HG5419P	A	19 dBi, 7in (17.8cm) Square, Integral N Female Connector	49.99	47.49	44.99	42.49	CALL

✓RoHS 5.8 GHz Patch Antennas

HG5811P	A	11 dBi, 4in (10.2cm) Square, Integral SMA Female Connector	49.99	44.99	39.99	34.99	29.99
HG5819P	A	19 dBi, 7in (17.8cm) Square, Integral N Female Connector	49.99	47.49	44.99	42.49	CALL
HG5158P	A	8 dBi, 4in (10.2cm) Square, Broadband, Integral SMA Female Connector	49.99	44.99	39.99	34.99	29.99
HG5158-23P	A	23 dBi, 12in (30.5cm) Square, Broadband, Integral N Female Connector	82.99	80.50	78.01	75.52	73.03

✓RoHS 4.9 to 5.8 GHz Broadband Patch Antenna


HG4958-23P	A	23 dBi, 12in (30.5cm) Square, Broadband, Integral N Female Connector	82.99	80.50	78.01	75.52	73.03
------------	---	--	-------	-------	-------	-------	-------

Call for special connectors and cable lengths



Informative e-mail newsletters

Our newsletters are packed with tips, tutorials, product info and downloads! L-com.com/Newsletter



HG2458-5P-135

STYLE

E

HG2458-14DP-3NF

STYLE

A

HG3514P-NF - Shown with HGX-PMT08 window mount kit. See L-com.com for more mounting options.

HG4911P

STYLE

A

HG5158-23P

STYLE

A

"STYLE" refers to shape of antenna in series.